



SOIC-20, 300 mils CASE 751BJ ISSUE O


DATE 19 DEC 2008



SYMBOL	MIN	NOM	MAX
А	2.36	2.49	2.64
A1	0.10		0.30
A2	2.05		2.55
b	0.31	0.41	0.51
С	0.20	0.27	0.33
D	12.60	12.80	13.00
Е	10.01	10.30	10.64
E1	7.40	7.50	7.60
е		1.27 BSC	
h	0.25		0.75
L	0.40	0.81	1.27
θ	0°		8°
θ1	5°		15°

TOP VIEW





Notes:

- (1) All dimensions are in millimeters. Angles in degrees.
- (2) Complies with JEDEC MS-013.

DOCUMENT NUMBER:	98AON34287E	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.	
DESCRIPTION:	SOIC-20, 300 MILS		PAGE 1 OF 1

onsemi and ONSEMi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.