

Comment	Designator	Footprint	Quantity
10uF_50V_10%_MLC-X7R_CAP1210	C1, C4, C5, C6, C8	CAP1210	5
100nF_50V_10%_MLC-X7R_CAP0603_M1	C2, C3, C12, C13, C14, C22, C23	CAP0603_M1	7
4.7uF_50V_10%_MLC-X7R_CAP1210	C7, C18, C19	CAP1210	3
4.7UF_0805_16V_X7R	C9, C10	CAP0805	2
4.7uF_100V_10%_MLC-X7S_CAP1210	C11, C15, C16	CAP1210	3
100NF_0805_100V_X7R	C17	CAP0805	1
100NF_0805_50V_X7R	C20	CAP0805	1
1nF_50V_10%_MLC-X7R_CAP0603	C21	CAP0603	1
MM5Z15VT1G	D1	ONSC-SOD-523-2-502-0	1
NRVTS8100PFS	D2	TO-277-3LD	1
691709710303	J_IN	691709710303	1
691709710305	J_OUT_1, J_OUT_2	691709710305	2
SPM7054VT-100M-D	L1	L_7,5mmX7mm	1
SPM4030T-3R3M-HZ	L2, L3	L_4,1mmX4mm	2
20kR_75V_100mW_1%_Thick Film_R0603	R1	R0603	1
10kR_75V_100mW_1%_Thick Film_R0603	R2	R0603	1
4.7R_R0603	R3, R4, R7, R9, R10, R11	R0603	6
0.100R_1206_1W_1% Kelvin	R5	R1206_Kelvin	1
10R_50V_100mW_0.5%_Thick Film_R0603	R6	R0603	1
0.0R_0805_0.1W	R8	R0805	1
NVTFS5116PLTWG	U4	WDFN8 3.3x3.3, P0.65_CASE 511AB	1
NCV78514	U6	TSSOP16_6.4X0.65MM_ EP	1
NVTFS6H860NTAG	U7	WDFN8 3.3x3.3, P0.65_CASE 511AB	1