

ON Semiconductor®

FJP13007 High Voltage Fast-Switching NPN Power Transistor

Features

- High Voltage High Speed Power Switch Application
- · High Voltage Capability
- · High Switching Speed
- Suitable for Electronic Ballast and Switching Mode Power Supply



Ordering Information

Part Number	Toj `~rk	Fackage	Racking Method
FJP13007TU	1136 7	TO 220 3L (Dual Gauge)	Rail
FJP13007H1TU	J1. 07-	TC-220 3L (Single Gauุระ)	Rail
FJP13007H1TU-F08 ^c	J1' 07-1	TO-2.20 3L (Dual Gauge)	Rail
FJP13007H2TU	J13007-2	iO-220 3L (L'ual Gauge)	Rail
FJP13007' _10-F08	J13007-2	TO-220 3⊾ (Dual Gauge)	Rail

bsoi 'e 'aximum Ratinge

So sees acceeding the absolute maximum ratings may damage the device. The device may not function or be operable to we the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to scresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only. Values are at $T_C = 25^{\circ}C$ unless otherwise noted.

Symbol	Parameter	Value	Unit
V _{CBO}	Collector-Base Voltage	700	V
V _{CEO}	Collector-Emitter Voltage	400	V
V_{EBO}	Emitter-Base Voltage	9	V
I _C	Collector Current (DC)	8	Α
I _{CP}	Collector Current (Pulse)	16	Α
I _B	Base Current (DC)	4	Α
P _C	Collector Dissipation (T _C = 25°C)	80	W
T _J	Junction Temperature	150	°C
T _{STG}	Storage Temperature Range	-65 to 150	°C

Electrical Characteristics

Values are at $T_C = 25^{\circ}C$ unless otherwise noted.

Symbol	Parameter	Conditions	Min.	Тур.	Max.	Unit
BV _{CEO}	Collector-Emitter Breakdown Voltage	$I_C = 10 \text{ mA}, I_B = 0$	400			V
I _{EBO}	Emitter Cut-Off Current	$V_{EB} = 9 \text{ V}, I_{C} = 0$			1	mA
h _{FE} 1	DC Current Gain ⁽¹⁾	$V_{CE} = 5 \text{ V}, I_{C} = 2 \text{ A}$	8		60	
h _{FE} 2	DC Current Gain ⁽¹⁾	$V_{CE} = 5 \text{ V}, I_{C} = 5 \text{ A}$	5		30	
		$I_C = 2 A, I_B = 0.4 A$			1.0	
V _{CE} (sat)	Collector-Emitter Saturation Voltage	I _C = 5 A, I _B = 1 A			2.0	V
		I _C = 8 A, I _B = 2 A				
\/ (cat)	Collector-Base Saturation Voltage	$I_C = 2 A, I_B = 0.4 A$			1.2	V. C
V _{BE} (sat)	Collector-base Saturation voltage	I _C = 5 A, I _B = 1 A			1	
f _T	Current Gain Bandwidth Product	$V_{CE} = 10 \text{ V}, I_{C} = 0.5 \text{ A}$	4		1,	NHz
C _{ob}	Output Capacitance	$V_{CB} = 10 \text{ V, } f = 0.1 \text{ N}$ 7		.0	C/1/4	pF
t _{ON}	Turn-On Time	V _{CC} = 125 V ₁ I _C = 4,		1	1.6	μs
t _{STG}	Storage Time	$I_{B1} = -I_{P2} =$		12	3.0	μs
t _F	Fall Time	R _L = 2t		D' .	73.7	195

Note:

1. Pulse test: $pw \le 300 \mu s$, duty cycle $\le 2\%$.

h_{FE} Classification

Classifica /	ار n	<u> </u>	H1 (-0	11-	H2	
1			15 ~ 23	× 0)/		26 ~ 39	

Typical Performance Characteristics




Figure 1. DC Current Gain





Figure 2. \ture_ion Vortage



igu 3. Collector Output Camacitance




Figure 4. Turn-On Time




Figure 5. Turn-Off Time




Figure 6. Forward Biased Safe Operating Area

Typical Performance Characteristics (Continued)





Figure 7. Reverse Biased Safe Operating Area



gure & Pow Derating



ON Semiconductor and III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns me rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdt/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages.

Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada

Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative