

NJD1718, NJVNJD1718

Power Transistors

PNP Silicon DPAK For Surface Mount Applications

Designed for high-gain audio amplifier and power switching applications.

Features

- Low Collector-Emitter Saturation Voltage
- High Switching Speed
- Epoxy Meets UL 94 V-0 @ 0.125 in
- NJV Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Collector-Base Voltage	V_{CB}	-50	Vdc
Collector-Emitter Voltage	V_{CEO}	-50	Vdc
Emitter-Base Voltage	V_{EB}	-5	Vdc
Collector Current - Continuous	I_C	-2	Adc
Collector Current - Peak	I_{CM}	-3	Adc
Base Current	I_B	-0.4	Adc
Total Device Dissipation @ $T_C = 25^\circ\text{C}$ Derate above 25°C	P_D	15 0.1	W W/ $^\circ\text{C}$
Total Device Dissipation @ $T_A = 25^\circ\text{C}$ (Note 1) Derate above 25°C	P_D	1.68 0.011	W W/ $^\circ\text{C}$
Operating and Storage Junction Temperature Range	T_J, T_{stg}	-65 to +150	$^\circ\text{C}$
ESD - Human Body Model	HBM	3B	V
ESD - Machine Model	MM	C	V

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

1. These ratings are applicable when surface mounted on the minimum pad sizes recommended.

THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Thermal Resistance Junction-to-Case Junction-to-Ambient (Note 2)	$R_{\theta JC}$ $R_{\theta JA}$	10 89.3	$^\circ\text{C}/\text{W}$



2. These ratings are applicable when surface mounted on the minimum pad sizes recommended.



ON Semiconductor®


<http://onsemi.com>

**SILICON
POWER TRANSISTORS
2 AMPERES
50 VOLTS
15 WATTS**



**DPAK
CASE 369C
STYLE 1**

MARKING DIAGRAM



- A = Assembly Location
- Y = Year
- WW = Work Week
- G = Pb-Free Device

ORDERING INFORMATION

Device	Package	Shipping [†]
NJD1718T4G	DPAK (Pb-Free)	2500 / Tape & Reel
NJVNJD1718T4G	DPAK (Pb-Free)	2500 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

NJD1718, NJVNJD1718

ELECTRICAL CHARACTERISTICS (T_C = 25°C unless otherwise noted)

Characteristic	Symbol	Min	Typ	Max	Unit
----------------	--------	-----	-----	-----	------

OFF CHARACTERISTICS

Collector-Emitter Breakdown Voltage (Note 3) (I _C = -10 mAdc, I _B = 0)	BV _{CEO}	-50		-	Vdc
Collector Cutoff Current (V _{CB} = -50 Vdc, I _E = 0)	I _{CBO}	-		-100	nAdc
Emitter Cutoff Current (V _{BE} = -5 Vdc, I _C = 0)	I _{EBO}	-		-100	nAdc

ON CHARACTERISTICS

DC Current Gain (Note 3) (I _C = -0.5 A, V _{CE} = 2 V) (I _C = -1.5 Adc, V _{CE} = 2 Vdc)	h _{FE}	70 40		240 -	-
Collector-Emitter Saturation Voltage (Note 3) (I _C = -1 A, I _B = -0.05 A)	V _{CE(sat)}	-	-0.2	-0.5	Vdc
Base-Emitter Saturation Voltage (Note 3) (I _C = -1 A, I _B = -0.05 Adc)	V _{BE(sat)}	-	-	-1.2	Vdc
Base-Emitter On Voltage (Note 3) (I _C = -1 Adc, V _{CE} = -2 Vdc)	V _{BE(on)}	-	-	-1.2	Vdc

DYNAMIC CHARACTERISTICS

Current-Gain - Bandwidth Product (Note 4) (I _C = -500 mAdc, V _{CE} = -2 Vdc, f _{test} = 10 MHz)	f _T	-	80	-	MHz
Output Capacitance (V _{CB} = 10 Vdc, I _E = 0, f = 0.1 MHz)	C _{ob}	-	33	-	pF
Switching Timers V _{CC} = -30 V, I _C = -1 A	t _{ON}	-	55	-	ns
	t _{STG}	-	320	-	
	t _f	-	40	-	

3. Pulse Test: Pulse Width = 300 μs, Duty Cycle ≈ 2%.

4. f_T = |h_{fe}| • f_{test}.

TYPICAL CHARACTERISTICS




Figure 1. DC Current Gain




Figure 2. Collector-Emitter Saturation Voltage




Figure 3. Base-Emitter Saturation Voltage




Figure 4. Base-Emitter Voltage




Figure 5. Capacitance




Figure 6. Current-Gain-Bandwidth Product

NJD1718, NJVNJD1718

TYPICAL CHARACTERISTICS




Figure 7. State Operating Area




Figure 8. Power Derating




Figure 9. Thermal Response

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales