

# SECO-LVDCDC3064-SIC-GEVB

## 6-18 Vdc Input Isolated SiC Gate Driver Supply +20 V / -5 V / 5 V with Automotive Qualified NCV3064 Controller Evaluation Board User's Manual

### Introduction

The SECO-LVDCDC3064-SIC-GEVB is an isolated supply for SiC drivers, providing the necessary stable voltage rails  $-5\text{ V} / 20\text{ V}$  for an efficient switching – as well as an additional  $5\text{ V}$  rail – over a wide input voltage range ( $6\text{ Vdc}$  to  $18\text{ Vdc}$ ). The converter is implemented as a primary side regulated flyback, with the feedback loop signal ( $1.25\text{ V}$ ) realized via an auxiliary winding regulated at  $5\text{ V}$  and a voltage divider. The design leverages the several merits of the NCV3064 regulator, enabling a low component count, compact and robust design. Among the features of this converter stand out – e.g. an internal temperature compensated reference, a controlled duty cycle oscillator with an active current limit circuit, driver and high current output switch. The board is realized with Automotive qualified parts and is pin compatible with commercial SiC DC/DC supplies, provisioning a ready to use plug-in solutions for power applications.

### Features

- Core Part – NCV3064 (Automotive) / NCP3064 (Industrial)
- Switching Frequency  $150\text{ kHz}$
- Input Voltage  $6\text{--}18\text{ VDC}$
- Output Voltage  $-5\text{ V} / 5\text{ V} / 20\text{ V}$
- Operation Mode DCM and CCM
- Output Current  $50\text{ mA}$  (for each Branch)
- Efficiency at Full Load  $67\%$
- Size  $26.24 \times 16.38 \times 16.06\text{ mm}$

### Transformer Basic Parameters

- Interwinding Capacitance  $6.4\text{ pF}$
- Dielectric Insulation  $4000\text{ VAC}$
- Inductance  $42\text{ }\mu\text{H}$
- Leakage Inductance  $650\text{ nH}$
- Safety Standard according to IEC62368-1 / IEC61558-2-16

### Applications


- Isolated SiC Driver Supply
- Automotive Powertrain Systems
- Automotive Auxiliary Power




ON Semiconductor®

[www.onsemi.com](http://www.onsemi.com)

## EVAL BOARD USER'S MANUAL



Top View



Bottom View

Figure 1. Board Layout

### Collateral

- [NCV3064](#)
- [SECO-LVDCDC3064-SIC-GEVB](#) – Order the Board

# SECO-LVDCDC3064-SIC-GEVB

## Scope and Purpose

The purpose of this design note is to present the design of an isolated supply for SiC drivers with qualified automotive part NCV3064 and transformer. The design was tested as described in this document but not qualified regarding safety

requirements or manufacturing and operation over the whole operating temperature range or lifetime. The hardware is intended for testing under laboratory conditions and by trained specialists only.

## Block Diagram




Figure 2. Block Diagram

## Design Overview

This development is a complete and ready to use SIC isolated gate driver supply consisting of automotive qualified parts – NCV3064 and transformer. The controller is also available with industrial grade NCP3064. Besides the power rails, the design provides the functional isolation is needed for level shifting when used with high-side gate drivers. Within a power system, the gate driver stage is crucial for an application to deliver the right performance reliably, as an unstable voltage supply to the gate driver will negatively impact the switching efficiency. The system needs to be simple but robust at the same time, in order to provision the required power without increasing the overall design complexity. The benefits of this proposed solution are:

- Simple, robust and low component count solution
- Stable performance across wide input voltage range (6 Vdc – 18 Vdc)
- Plug-in header for easy integration
- AEC-Q qualified parts
- IEC standard transformer

## Flyback Topology and Voltage Levels

The flyback topology enables multiple voltage output and isolated power with a simple layout and low components count. This power supply supports an VDC input of 6 V to 18 V and provisions three voltage output rails: +20 V / -5 V to be used for the SiC switching and +5 V as an auxiliary power rail. The supply is operated in Discontinuous Conduction Mode (DCM) and Continuous Conduction

Mode (CCM) depending on the load with regulating the primary auxiliary winding at 5 V. The transformer transmission ratio is adjusted to deliver stable voltage output rails at +20 V / -5 V and 5 V.

## NCV3064 (NCP3064)

The NCP3064 Buck Boost Inverting Switching Regulator is a higher frequency upgrade to the popular MC33063A and MC34063A monolithic dc-dc hysteretic converters. This converter embeds multiple relevant features in a small footprint (DFN-8 package), standing out the stable performance over a wide input voltage range. That is a main advantages to consider in this application. Among the features of this converter stand out an internal temperature compensated reference, a controlled duty cycle oscillator with an active current limit circuit, driver and high current output switch. In this design, the ON/OFF pin is externally connected to the input voltage rail. UVLO or OFF control could be implemented with additional logic circuitry, but this functionality is not covered in this design. The NCV3064 is automotive qualified (AEC) and the NCP3064 is available for industrial grade.

## Pinout Header (Plug-in)

The pinout header is intended to provide an easy integration interface to development boards or series boards. Pinout is compatible with MORNSUN QA01C with one additional pin P5V, which can be used as auxiliary power supply. See Layout section for more information.

# SECO-LVDCDC3064-SIC-GEVB

## SPECIFICATION

| Parameters  | Values   |
|---|--|
| <b>Input</b>  |  |
| Voltage   | 6–18 VDC   |
| Current   | 400 mA ( $V_{in} = 6\text{ V}$ ), 125 mA ( $V_{in} = 18\text{ V}$ )                                |
| <b>Output</b>   |  |
| Power   | 1.5 W  |
| Voltage   | –5 / 5 / 20 VDC  |
| Current per branch  | 50 mA  |
| Total current   | 150 mA   |
| Efficiency at full load   | 67% ( $V_{in} = 15\text{ V}$ )   |
| Temperature at full load  | 98°C ( $V_{in} = 6\text{ V}$ ), 74.5°C ( $V_{in} = 15\text{ V}$ ), 76°C ( $V_{in} = 18\text{ V}$ ) |
| <b>Control</b>  |  |
| Core part   | NCV3064  |
| Topology  | Flyback  |
| Switching frequency   | 150 kHz  |
| Operation mode  | DCM and CCM  |
| Primary side peak current   | 1.1 A  |
| <b>Construction</b>   |  |
| Board size  | 26.24 x 16.38 x 16.06 mm   |
| <b>Transformer</b>  |  |
| Interwinding capacitance  | 6.4 pF   |
| Dielectric insulation   | 4000 VAC   |
| Inductance  | 42 $\mu\text{H}$   |
| Leakage inductance  | 650 nH   |
| Safety standard   | IEC62368–1 / IEC61558–2–16   |
| <b>Application</b>  |  |
| Isolated SiC driver supply, automotive powertrain systems, automotive auxiliary power |  |

# SECO-LVDCDC3064-SIC-GEVB

## Schematic




Figure 3. Evaluation Board Schematic


TEST REPORT

This section presents the results of the tests conducted on the power supply. The aim of these is to demonstrate The evaluated parameters of the design are:


- Output voltage at different loads and input voltages
- Temperature performance
- Cross regulation measurements
- Output voltage ripple
- Load transients
- Line regulation
- Efficiency

Output Voltages Measurement


In this section output voltages of all branches in relation to load current and different input voltages are showed.



a)




b)




c)


Figure 4. Measurement of Output Voltage for Load Current and 6 V Input Voltage: a) 20 V Branch, b) 5 V Branch, c) -5 V Branch



a)




b)



c)

Figure 5. Measurement of Output Voltage for Load Current and 15 V Input Voltage: a) 20 V Branch, b) 5 V Branch, c) -5 V Branch


# SECO-LVDCDC3064-SIC-GEVB



**Figure 6. Measurement of Output Voltage for Load Current and 18 V Input Voltage: a) 20 V Branch, b) 5 V Branch, c) -5 V Branch**

## Temperature Measurement

Following pictures are showing temperature of converter in full load state (50 mA for each branch) for different input voltages. The working time of device to reach equilibrium state is 20 minutes.



**Figure 7. Temperature Measurement During Full Load (50 mA) on Each Branch: a) Input Voltage 6 V, b) Input Voltage 15 V, c) Input Voltage 18 V**

# SECO-LVDCDC3064-SIC-GEVB

## Cross Regulation Measurement

The flyback is regulated via the primary auxiliary transformer winding at 5 V. Following table is showing

values of output voltages for different output loading. Moreover, the test is performed for values of input voltage 6 V, 15 V, 18 V.

**Table 1. VALUES OF OUTPUT VOLTAGES – CROSS REGULATION MEASUREMENT**

| Vin = 6 V                                   |      |   |  |   |
|---|------|---|--|---|
| P5V Full Load (50 mA), N5V and P20V No Load |      | P5V No Load, N5V and P20V Full Load (50 mA) |  | P5V and N5V No Load, P20V Full Load (50 mA) |
| Vout_P20V (V)                               | 21.1 | 20.36                                       |  | 20.13                                       |
| Vout_P5V (V)                                | 4.44 | 5.2   |  | 5.19  |
| Vout_N5V (V)                                | -5.2 | 4.93  |  | 5.19  |
| Vin = 15 V                                  |      |   |  |   |
| P5V Full Load (50 mA), N5V and P20V No Load |      | P5V No Load, N5V and P20V Full Load (50 mA) |  | P5V and N5V No Load, P20V Full Load (50 mA) |
| Vout_P20V (V)                               | 21.1 | 20.21                                       |  | 20.01                                       |
| Vout_P5V (V)                                | 4.36 | 5.19  |  | 5.19  |
| Vout_N5V (V)                                | -5.2 | -4.9  |  | -5.19                                       |
| Vin = 18 V                                  |      |   |  |   |
| P5V Full Load (50mA), N5V and P20V No Load  |      | P5V No Load, N5V and P20V Full Load (50 mA) |  | P5V and N5V No Load, P20V Full Load (50 mA) |
| Vout_P20V (V)                               | 21.1 | 20.2  |  | 19.99                                       |
| Vout_P5V (V)                                | 4.33 | 5.2   |  | 5.2   |
| Vout_N5V (V)                                | -5.2 | -4.9  |  | -5.2  |

## Measurement of Output Voltage Ripple

The output voltage ripple measurement is done on P20V and N5V branch. Results for P5V branch are considered to be the same as for the N5V ones. Used conditions are: no load, half load and full load on all of the three branches and additional condition where just measured branch is fully loaded and the other two have no load. The last one condition is the worst case regarding the voltage ripple. All of these measurements are done for input voltage value 6 V, 15 V, 18 V. Results can be seen in the table 2. Ripple is calculated as  $(V_{max}-V_{min})/V_{DC} \cdot 100$ , where  $V_{max}$  is the maximal value of voltage on given output and  $V_{min}$  is the minimal value. The worst case of voltage ripple can also be seen in the Figure 8.

**Table 2. OUTPUT VOLTAGE RIPPLE FOR DIFFERENT CONDITIONS: a) P20V Branch, b) N5V Branch**


|             | No Load | 50% Load | 100% Load | 100% Load just on P20V Branch |
|-------------|---------|----------|-----------|-------------------------------|
| Vin = 6 V   |         |          |           |                               |
| Vripple [%] | 0.4     | 1.08     | 1.72      | 1.9                           |
| Vin = 15 V  |         |          |           |                               |
| Vripple [%] | 0.7     | 1.26     | 2.17      | 2.23                          |
| Vin = 18 V  |         |          |           |                               |
| Vripple [%] | 0.8     | 1.44     | 2.21      | 2.42                          |

a)


|             | No Load | 50% Load | 100% Load | 100% Load just on N5V Branch |
|-------------|---------|----------|-----------|------------------------------|
| Vin = 6 V   |         |          |           |                              |
| Vripple [%] | 0.29    | 1.78     | 2.52      | 5.31                         |
| Vin = 15 V  |         |          |           |                              |
| Vripple [%] | 0.5     | 2.13     | 2.89      | 5.95                         |
| Vin = 18 V  |         |          |           |                              |
| Vripple [%] | 0.67    | 2.22     | 3.5       | 7.24                         |

b)

# SECO-LVDCDC3064-SIC-GEVB



a)




b)


**Figure 8. Output Voltage Ripple for Worst Cases:**  
**a) P20V Branch – Vin = 18 V, just P20V is fully loaded,**  
**b) N5V Branch – Vin = 18 V, just N5V is fully loaded**

## Short Circuit Measurement


The short circuit test is done during no load condition where always just one branch is short circuited. The waveforms of output voltages during the test are in the Figure 9.



a)



b)



c)


**Figure 9. Short Circuit Tests (Yellow – P20V, Green – P5V, Blue – N5V): a) Short Circuit on P20V, b) Short Circuit on N5V, c) Short Circuit on P5V**




# SECO-LVDCDC3064-SIC-GEVB

## Load Transients Measurement

The load transient measurements are done for P20V and N5V branch. During the test just measured branch is loaded alternately with full load (50 mA) for 1.5 ms and no load for 1.5 ms, the other two have no load. Results are in the Figure 10.



a)




b)


Figure 10. Load Transients Measurement:  
a) P20V Branch, b) N5V Branch

## Line Regulation Measurement

In this test the reaction of the output voltages on the input voltage change from 6 V to 18 V for 1.5 ms is measured. The test is performed for no load and full load condition on all of the branches. Results can be seen in the Figure 11.



a)



b)

Figure 11. Line Regulation Measurement  
(Blue – Vin, N5V, Green – P5V, Yellow – P20V):  
a) No Load Condition, b) Full Load Condition

## Efficiency Measurement

Efficiency is measured for different load condition from 5 mA to 50 mA (full load for one branch) with step 5 mA. The branches are loaded simultaneously. It means that the resulting load is from 15 mA to 150 mA. Results can be seen in the Figure 12.




Figure 12. Efficiency for Different Output Load

# SECO-LVDCDC3064-SIC-GEVB

## Transformer Design

The transformer is developed according to IEC62368-1 /IEC61558-2-16 safety standards and working in Discontinuous Current Mode (DCM) and Continuous Current Mode (CCM) depending on load conditions. The

used flyback transformer is an off-the-shelf part from Würth Elektronik, which ensures the needed voltages, isolation according to the aforementioned standards and low interwinding capacitance.




Figure 13. Drawing and Parameters of Used Transformer

## SECO-LVDCDC3064-SIC-GEVB

### Development Resources and Tools

Collateral, development files and other development resources listed below are available at [SECO-LVDCDC3064-IGBT-GEVB](#)

- Schematics
- BOM (below as well)
- Manufacturing files
- PCB layout (below as well)
- Altium files
- Simulation model (below as well)

**Table 3. BILL OF MATERIALS**

| #   | Designator                                 | Comment        | Description  | Manufacturer     | Manufacturer Part Number |
|-----|--|----------------|--|------------------|--------------------------|
| 1.  | C1, C2, C4, C6, C8, C9, C10, C11, C12, C13 | 10 $\mu$ F     | SMD Multilayer Ceramic Capacitor, 10 $\mu$ F, 25 V, 0805 [2012 Metric], $\pm$ 10%, X7S, CGA Series                               | TDK              | CGA4J1X7S1E106K125 AE    |
| 2.  | C3   | 220 pF         | Multilayer Ceramic Capacitors ML-CC – SMD/SMT 50V 220pF 0603 X7R 10% AEC-Q200  | KEMET            | C0603C221K5RACAUTO       |
| 3.  | C5   | 2.2 $\mu$ F    | GRT188C81E225KE13D – SMD Multilayer Ceramic Capacitor, 2.2 $\mu$ F, 25 V, 0603 [1608 Metric], $\pm$ 10%, X6S, GRT Series, Murata | Murata           | GRT188C81E225KE13D       |
| 4.  | C7   | 2.2 nF         | Multilayer Ceramic Capacitors ML-CC – SMD/SMT CGA 0603 50V 2200pF X7R 10% AEC-Q200   | TDK              | CGA3E2X7R1H222K080 AA    |
| 5.  | CON1                                       | 613 002 110 21 | PTH right angle male header 2 pins 2.54 mm pitch Würth Elektronik  | Würth Elektronik | 61300211021              |
| 6.  | CON2                                       | 61300411021    | WR-PHD 2.54 mm THT Angled Pin Header 1x4   | Würth Elektronik | 61300411021              |
| 7.  | D1   | SZMMSZ18T1G    | Zener Single Diode, 18 V, 500 mW, SOD-123, 5 %, 2 Pins, 150 °C   | ON Semiconductor | SZMMSZ18T1G              |
| 8.  | D2, D3, D4, D5, D6                         | NRVTS2H60E     | Trench Schottky Rectifier, Very Low Leakage 2A, 60V ON Semiconductor   | ON Semiconductor | NRVTS2H60ESFT1G          |
| 9.  | IC1  | NCV3064MNTXG   | Buck / Boost / Inverting Converter, Switching Regulator, 1.5 A, with On/Off Function   | ON Semiconductor | NCV3064MNTXG             |
| 10. | R1   | 1k3            | SMD thick film resistor 1k3 0603 1% 100 mW Panasonic   | Panasonic        | ERJ3EKF1301V             |
| 11. | R2   | 7k5            | SMD thick film resistor 7k5 0603 1% 100 mW Panasonic   | Panasonic        | ERJ3EKF7501V             |
| 12. | R3   | 0R22           | SMD Current Sense Resistor, 0.22 ohm, ERJ3R Series, 0603 [1608 Metric], 100 mW, $\pm$ 1%, Thick Film, Panasonic                  | Panasonic        | ERJ3RQFR22V              |
| 13. | R4   | 2k37           | SMD thick film resistor 2k26 0603 1% 100 mW Panasonic  | Panasonic        | ERJ3EKF2261V             |
| 14. | R5   | 10k            | SMD thick film resistor 10k 0603 1% 100 mW Panasonic   | Panasonic        | ERJ3EKF1002V             |
| 15. | R6, R7                                     | 5k1            | SMD thick film resistor 5k1 0603 1% 100 mW Panasonic   | Panasonic        | ERJ3EKF5101V             |
| 16. | TR1  | 750319282      | Custom transformer Flyback converter $U_{in}=15V$ $U_{out1}=20V$ $U_{out2}=-5V$ $U_{out3}=5V$ $U_{out4\_aux}=5V$                 | Würth Elektronik | 750319282                |

# SECO-LVDCDC3064-SIC-GEVB

## Layout

The board is designed in two layers with size of 26.24 x 16.38 x 16.06 mm. The pinout is compatible with commercial DC/DC block converters for gate drivers

supply, and includes one additional pin P5V, which can be used as auxiliary power supply. Figure of top, bottom layer and front view can be seen in the Figure 14.




Figure 14. Board Layout: a) Top Side with Dimensions, b) Bottom Side, c) Front Side. Header is Pin Compatible with Standard DC/DC Isolated Supply Bricks.

# SECO-LVDCDC3064-SIC-GEVB

## Simulation Model

This model is created and used as a behavioral one to get the first iteration of design. Schematic from SIMetrix can be

seen in the Figure 15. Figure 16 and 17 is showing output voltages during full load state for input voltage 6 and 15 V.




Figure 15. Simulation Model




Figure 16. Output Voltages for  $V_{in} = 6$  V

# SECO-LVDCDC3064-SIC-GEVB




Figure 17. Output Voltages for  $V_{in} = 15\text{ V}$

## References

- NCP3064—D. Buck / Boost / Inverting Converter, Switching Regulator, 1.5 A, with On/Off Function.  
[Link](#)

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

The evaluation board/kit (research and development board/kit) (hereinafter the "board") is not a finished product and is not available for sale to consumers. The board is only intended for research, development, demonstration and evaluation purposes and will only be used in laboratory/development areas by persons with an engineering/technical training and familiar with the risks associated with handling electrical/mechanical components, systems and subsystems. This person assumes full responsibility/liability for proper and safe handling. Any other use, resale or redistribution for any other purpose is strictly prohibited.

**THE BOARD IS PROVIDED BY ONSEMI TO YOU "AS IS" AND WITHOUT ANY REPRESENTATIONS OR WARRANTIES WHATSOEVER. WITHOUT LIMITING THE FOREGOING, ONSEMI (AND ITS LICENSORS/SUPPLIERS) HEREBY DISCLAIMS ANY AND ALL REPRESENTATIONS AND WARRANTIES IN RELATION TO THE BOARD, ANY MODIFICATIONS, OR THIS AGREEMENT, WHETHER EXPRESS, IMPLIED, STATUTORY OR OTHERWISE, INCLUDING WITHOUT LIMITATION ANY AND ALL REPRESENTATIONS AND WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, TITLE, NON-INFRINGEMENT, AND THOSE ARISING FROM A COURSE OF DEALING, TRADE USAGE, TRADE CUSTOM OR TRADE PRACTICE.**

**onsemi** reserves the right to make changes without further notice to any board.

You are responsible for determining whether the board will be suitable for your intended use or application or will achieve your intended results. Prior to using or distributing any systems that have been evaluated, designed or tested using the board, you agree to test and validate your design to confirm the functionality for your application. Any technical, applications or design information or advice, quality characterization, reliability data or other services provided by **onsemi** shall not constitute any representation or warranty by **onsemi**, and no additional obligations or liabilities shall arise from **onsemi** having provided such information or services.

**onsemi** products including the boards are not designed, intended, or authorized for use in life support systems, or any FDA Class 3 medical devices or medical devices with a similar or equivalent classification in a foreign jurisdiction, or any devices intended for implantation in the human body. You agree to indemnify, defend and hold harmless **onsemi**, its directors, officers, employees, representatives, agents, subsidiaries, affiliates, distributors, and assigns, against any and all liabilities, losses, costs, damages, judgments, and expenses, arising out of any claim, demand, investigation, lawsuit, regulatory action or cause of action arising out of or associated with any unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of any products and/or the board.

This evaluation board/kit does not fall within the scope of the European Union directives regarding electromagnetic compatibility, restricted substances (RoHS), recycling (WEEE), FCC, CE or UL, and may not meet the technical requirements of these or other related directives.

FCC WARNING – This evaluation board/kit is intended for use for engineering development, demonstration, or evaluation purposes only and is not considered by **onsemi** to be a finished end product fit for general consumer use. It may generate, use, or radiate radio frequency energy and has not been tested for compliance with the limits of computing devices pursuant to part 15 of FCC rules, which are designed to provide reasonable protection against radio frequency interference. Operation of this equipment may cause interference with radio communications, in which case the user shall be responsible, at its expense, to take whatever measures may be required to correct this interference.

**onsemi** does not convey any license under its patent rights nor the rights of others.

LIMITATIONS OF LIABILITY: **onsemi** shall not be liable for any special, consequential, incidental, indirect or punitive damages, including, but not limited to the costs of requalification, delay, loss of profits or goodwill, arising out of or in connection with the board, even if **onsemi** is advised of the possibility of such damages. In no event shall **onsemi**'s aggregate liability from any obligation arising out of or in connection with the board, under any theory of liability, exceed the purchase price paid for the board, if any.

The board is provided to you subject to the license and other terms per **onsemi**'s standard terms and conditions of sale. For more information and documentation, please visit [www.onsemi.com](http://www.onsemi.com).

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at [www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)