

AR0830

Image Sensor, 8.3 MP, Rolling Shutter, Hyperlux™ LP

Product Overview

For complete documentation, see the data sheet.

AR0830, belongs to **onsemi's** Hyperlux LP product family, is a 1/2.9inch Back-Side Illuminated (BSI) Stacked CMOS digital image sensor with a 3840 x 2160 activepixel array. This advanced sensor captures images in either linear or enhanced Dynamic Range (eDR) modes, with a rollingshutter readout. The AR0830 is architected & designed to deliver highquality performance consuming very low power. It is supported by a 1.4 μm BSI pixel from **onsemi** and delivers excellent performance in lowlight & NIR wavelengths. The features of the AR0830 provides a powerful data capturing device at the edge that can be programmed through several options to deliver optimal bandwidth at very low power.

Features

- Lowest Power Consumption among Comparable Offerings in the Industry
- Enhanced NIR Response in 850nm & 940nm Wavelength
- Wake on Motion (WOM)
- Multiple Subsampling Modes - Binning, summing, Skipping, Windowing
- Multiple Functional Modes - Global Reset Release (GRR), Trigger, Context Switching
- enhanced Dynamic Range (eDR) & Line Interleaved HDR (LI-HDR) Modes

Applications









- Videoconferencing
- Smart Access
- Virtual & Augmented Reality
- Machine Vision
- Retail Analytics


End Products

- VC Endpoints, Webcam
- Video Doorbells
- AR/VR/XR Headsets
- Machine Vision Cameras
- Retail In-store Cameras

Part Electrical Specifications

Product	Status	Compliance	Type	Me-gapi-xels	Fra-me-Rate (fps)	Opti-cal-For-mat	Shu-tter-Type	Pixe-l-Size (µm)	Out-put-Inter-face	Col-or	Fam-ily	Pac-kage-Type	Cas-e-Out-line	MS-L-Type	MS-L-Temp (°C)	Con-tain-er-Type	Con-tain-er-Qty.
AR0830CSSC11 SMD20	Active	H Pb	CM OS	8.3	60	1/3 inch	Electron ic Rolling and Global Reset Release	1.4 x 1.4	MIPI	RGB	Hyperlux LP	-		NA	0	MTFRM	1
AR0830CSSC11 SMD20-RC1	Active	Pb	CM OS	8.3	60	1/3 inch	Electron ic Rolling and Global Reset Release	1.4 x 1.4	MIPI	RGB	Hyperlux LP	-		NA	0	MTFRM	1
AR0830CSSC11 SMKA1-CP	Active	H Pb	CM OS	8.3	60	1/3 inch	Electron ic Rolling and Global Reset Release	1.4 x 1.4	MIPI	RGB	Hyperlux LP	OD CSP 59 6.41 x3.9 1x0.63, 0.5 OP	570 AY. PDF	4	245	CTRAY	3000
AR0830CSSC11 SMKA1-CP2	Active	H Pb	CM OS	8.3	60	1/3 inch	Electron ic Rolling and Global Reset Release	1.4 x 1.4	MIPI	RGB	Hyperlux LP	OD CSP 59 6.41 x3.9 1x0.63, 0.5 OP	570 AY. PDF	4	245	CTRAY	50
AR0830CSSC3 5SMD20	Active	H Pb	CM OS	8.3	60	1/3 inch	Electron ic Rolling and Global Reset Release	1.4 x 1.4	MIPI	RGB	Hyperlux LP	-		NA	0	MTFRM	1
AR0830CSSC3 5SMD20-RC1	Active	H Pb	CM OS	8.3	60	1/3 inch	Electron ic Rolling and Global Reset Release	1.4 x 1.4	MIPI	RGB	Hyperlux LP	-		NA	0	MTFRM	1
AR0830CSSC3 5SMKA1-CP	Active	H Pb	CM OS	8.3	60	1/3 inch	Electron ic Rolling and Global Reset Release	1.4 x 1.4	MIPI	RGB	Hyperlux LP	OD CSP 59 6.41 x3.9 1x0.63, 0.5 OP	570 AY. PDF	4	245	CTRAY	3000

AR0830CSSC35SMKA1-CP2	Active		CMOS	8.3	60	1/3 inch	Electronic Rolling and Global Reset Release	1.4 x 1.4	MIPI	RGB	Hyperlux LP	OD CSP 59 6.41 x3.9 1x0.63, 0.5 OP	570 AY. PDF	4	245	CTR AY	50
AR0830CSSH11SMD20	Active		CMOS	8.3	60	1/3 inch	Electronic Rolling and Global Reset Release	1.4 x 1.4	MIPI	RGB-IR	Hyperlux LP	-		NA	0	MTFRM	1
AR0830CSSH11SMD20-RC1	Active		CMOS	8.3	60	1/3 inch	Electronic Rolling and Global Reset Release	1.4 x 1.4	MIPI	RGB-IR	Hyperlux LP	-		NA	0	MTFRM	1
AR0830CSSH11SMKA1-CP	Active		CMOS	8.3	60	1/3 inch	Electronic Rolling and Global Reset Release	1.4 x 1.4	MIPI	RGB-IR	Hyperlux LP	OD CSP 59 6.41 x3.9 1x0.63, 0.5 OP	570 AY. PDF	4	245	CTR AY	3000
AR0830CSSH11SMKA1-CP2	Active		CMOS	8.3	60	1/3 inch	Electronic Rolling and Global Reset Release	1.4 x 1.4	MIPI	RGB-IR	Hyperlux LP	OD CSP 59 6.41 x3.9 1x0.63, 0.5 OP	570 AY. PDF	4	245	CTR AY	50
AR0830CSSH35SMKA1-CP	Active		CMOS	8.3	60	1/3 inch	Electronic Rolling and Global Reset Release	1.4 x 1.4	MIPI	RGB-IR	Hyperlux LP	OD CSP 59 6.41 x3.9 1x0.63, 0.5 OP	570 AY. PDF	4	245	CTR AY	3000
AR0830CSSH35SMKA1-CP2	Active		CMOS	8.3	60	1/3 inch	Electronic Rolling and Global Reset Release	1.4 x 1.4	MIPI	RGB-IR	Hyperlux LP	OD CSP 59 6.41 x3.9 1x0.63, 0.5 OP	570 AY. PDF	4	245	CTR AY	50
AR0830CSSM11SMKA1-CP	Active		CMOS	8.3	60	1/3 inch	Electronic Rolling and Global Reset Release	1.4 x 1.4	MIPI	Mono	Hyperlux LP	OD CSP 59 6.41 x3.9 1x0.63, 0.5 OP	570 AY. PDF	4	245	CTR AY	3000

AR0830CSSM11 SMKA1-CP2	Active		CMOS	8.3	60	1/3 inch	Electronic Rolling and Global Reset Release	1.4 x 1.4	MIPI	Mono	Hyperlux LP	OD CSP 59 6.41 x 3.91 x 0.63, 0.50P	570 AY. PDF	4	245	CTRAY	50
---------------------------	--------	---	------	-----	----	----------	---	-----------	------	------	-------------	-------------------------------------	-------------	---	-----	-------	----