

## ARX383CS

# 1/8-inch 0.3 Mp Global Shutter CMOS Digital Image Sensor

## Product Overview

For complete documentation, see the data sheet.

The ARX383CS is a 1/8inch 0.3Mp VGA CMOS digital image sensor with an activepixel array of 640 x 480. It incorporates an innovative global shutter pixel design optimized for accurate and fast capture of moving scenes at 120 frame per second, full resolution. The sensor produces clear, low noise images in both lowlight and bright scenes. It includes sophisticated camera functions such as adjustable auto-exposure control, auto black-level correction, windowing, skipping, pixelbinning, and, both video & single frame modes. It is programmable through a simple twowire serial interface. The ARX383CS produces clear, sharp digital pictures with an industry leading Global Shutter Efficiency, and its ability to capture both continuous video and single frames makes it the perfect choice for a wide range of applications, including scanning, autonomous mobility, AR/VR, AIoT and industrial quality control.

## Features

- Best in Class Global Shutter Efficiency
- Low Operational Power
- Small Form Factor
- Built-In Statistics Engine
- Multiple Subsampling Modes

## Applications

- Barcode Scanning
- People Counting
- Machine Vision
- Autonomous Mobility
- AR/VR/MR

## End Products

- Barcode Readers
- People Counters
- Machine Vision Cameras
- AR/VR/MR Headsets
- Payment Terminals with Face-Access