

NCP1680

Totem-Pole Critical Conduction Mode (CrM) Power Factor Correction Controller

Product Overview

For complete documentation, see the data sheet.

The NCP1680 is a CrM PFC controller IC designed to drive the bridgeless totem-pole PFC topology. The bridgeless totem-pole PFC is a power factor correction architecture that consists of a fast switching leg driven at the PWM switching frequency and a second leg that operates at the AC line frequency. This topology eliminates the diode bridge present at the input of a conventional PFC circuit, allowing significant improvement in the power stage efficiency.

Features

- Totem Pole PFC Topology Eliminates Input Diode Bridge
- Critical Conduction Mode (CrM) Operation
- Discontinuous Conduction Mode (DCM) with Valley Turn On Under Light Load Condition
- Frequency Foldback in DCM With 25 kHz Minimum Frequency
- Skip Mode in Very Light Load Condition
- Proprietary Current Sense Scheme
- Digital Voltage Loop Compensation
- AC Line Monitoring Circuit & AC Phase Detection
- Near Unity Power Factor in All Operating Modes
- PFC OK Indicator

For more features, see the data sheet




Applications

- Power Factor Correction
- Offline Power Supply

End Products

- Industrial Power Supplies
- Telecom 5G Power
- Networking Power
- Gaming Console Power Supplies
- UHD TV Power Supplies

Part Electrical Specifications

Product	Status	Compliance	PF C Mode	Frequency Operation	Control Mode	Topology	f_{sw} Typ (kHz)	V_{CC} Max (V)	Drive Cap. (mA)	UVLO (V)	Latch	UVP	Inhibition	Package Type	Case Outline	MSL Type	MSL Temp (°C)	Container Type	Container Qty.
NCP1680AAD1R2G	Active		CRM	Variable	Current/Voltage Mode	Totem Pole	Variable	30	100/100	10.5	Yes	Yes	No	SOIC-16	751B-05.PDF	1	260	REEL	2500
NCP1680ABD1R2G	Active		CRM	Variable	Current/Voltage Mode	Totem Pole	Variable	30	100/100	10.5	Yes	Yes	No	SOIC-16	751B-05.PDF	1	260	REEL	2500
NCP1680ACD1R2G	Active		CRM	Variable	Current/Voltage Mode	Totem Pole	Variable	30	100/100	10.5	Yes	Yes	No	SOIC-16	751B-05.PDF	1	260	REEL	2500