



System Solution Guide - Preview

Switched-Mode Power Supply (SMPS)



onsemi.com



Table of Contents

Get Latest
Version

Overview

Applications

03

Market Information & Trend

Market Outlook & Technical Trends

04

System Implementation

SMPS System Architecture

05

System Description

Standards, PFC & DC-DC Stage

06

Current Control Mode

07

Solution Overview

Block Diagrams - Bridge PFC + Flyback & Totem Pole PFC + LLC

08

Easy to Use SMPS Matrix

09

Topologies

10

Power Supply Reference Designs

12

EliteSiC MOSFET

13

T10 LV-MV MOSFET & iGaN

14

SiC Gate Driver

15

PFC Controller

16

Secondary Side LLC and SR Controller

17

Recommended Products

18

Development Tools and Resources

22

onsemi™



Register now to unlock all System Solution Guides

Full Guide Preview

Get Latest Version



1



2



3



4




5



6




7




8



9




10



11




12



13



14



15



16



17



18



19




20


Block Diagram - SMPS

Get Latest Version


Block Diagram - SMPS (Bridge PFC + Flyback Converter)



Block Diagram - SMPS (Totem Pole PFC + LLC Resonant Converter)



*Optional



Use our Interactive Block Diagrams Tool



Open IBD Tool

SMPS Matrix

Get Latest Version

Easy to Use SMPS Matrix

onsemi's SMPS Matrix (Table 2) offers a comprehensive range of power management options tailored for various applications. These solutions cover power ranges from 5W to over 3kW. For instance, the matrix includes controllers, gate drivers, and switches designed for applications such as Power Factor Correction (PFC), Active Clamp Flyback (ACF), Quasi Resonant Flyback (QR), and Synchronous Rectifier Controller (SRC) configurations. These solutions are optimized to provide reliable and efficient power conversion, catering to diverse needs from low-power USB-C PD designs to high-power industrial and telecom applications.

By leveraging advanced technologies like SiC and iGaN, **onsemi** ensures the SMPS Matrix solutions deliver superior performance and energy efficiency for a wide range of power management requirements.

Table 2: **onsemi** "Easy to Use" SMPS Matrix

Power Range (W)	Power Density Rating	Rectifier	Primary Side										Secondary Side		USB-C/PD
			PFC			ACF			QR Flyback		LLC		Controller	SR Switch	
			Controller	Power Switch	Slow / Fast Leg Gate Drive	Controller	HV (Q2) Gate Drive	Power Switch	Controller	Power Switch	Controller	HS/LS Switch / Gate Drive			
1kW to >3kW (24-48V)	Ultra High	w/o	NCP1681 (CCM)	SiC iGaN	NCP51530 NCP51561	NA					NCP13994		NCP4318	NA	
	High	DFB25100 DFB2580	FAN9672 FAN9673 (CCM)	HV MOSFET	NA					NCP4390	SiC /iGaN NCP51561	NA			
350W to 1kW (12V-24V)	Ultra High	w/o	NCP1681	SiC iGaN	NCP51530 NCP51561	NA					NCP13994		NCP4318		
	High	DFB20100 DFB2080	NCP1618 (MM)	HV MOSFET	NA					HV MOSFET					
200W to 350W (12V-24V)	Ultra High	w/o	NCP1680 (TP CrM)	SiC iGaN	NCP51530 NCP51561	NA									
	Low Profile	DFB20100 DFB2080	NCP1632 (CrM)	SiC /iGaN NCD 57000	NA						HV MOSFET				
	High		NCP1616 (CrM)	HV MOSFET	NA						HV MOSFET				
70W to 200W (12V-24V)	Ultra High	GBU8M GBU8K	NCP1623	SiC /iGaN NCD 57000	NA	NCP1568	NCP51561	SiC iGaN	NA				NCP4307	FUSB15101	
	High	GBU6M GBU6K		HV MOSFET	NA			NCP1343	HV MOSFET	NA					
65W (3.3V-21V)	High	GBU4M GBU4K	NA			NCP1345	HV MOSFET	NA		NCP4306					
25W to 50W	High		Switchers: NCP11184 / NCP11185 / NCP11187												
5W to 25W	High	DF10S DF08S	Switchers: NCP1072 / NCP1075 / NCP1076 / NCP1077												

NA: Not Applicable



Figure 3: Applications per Power Level

Reference Designs for SMPS

Get Latest Version

Power Supply Reference Designs

onsemi offers a versatile range of SMPS solutions that cater to various power requirements, spanning from 65W to over 3kW. Their product lineup includes controllers, gate drivers, MOSFETs, and advanced WBG materials like SiC and GaN. These solutions are designed to provide high efficiency, reliability, and performance across a wide range of applications, including USB-C PD, industrial power supplies, and cloud server power supplies.

3kW EliteSiC Totem Pole PFC + LLC PSU

- High power density topology - Totem Pole PFC + LLC
- $V_{in} = 85V-264V$, $V_{out} = 54V$, $I_{out} = 55.5A$
- PFC Efficiency > 98% @100% load
- System Peak Efficiency > 94% @115VAC; > 96% @230VAC
- PCBA size: 280mm x 110mm x 38mm
- Featuring products: Multi-mode TP PFC [NCP1681](#), LLC with SR Controller [NCP4390](#), Isolated HB Gate Driver [NCP51561](#), 650V SiC MOSFET [NTHL045N065SC1](#)
- Application: Industrial PSU

[Download Whitepaper](#)




Figure 4: 3kW Totem Pole PFC + LLC PSU Evaluation Board

1 kW Universal Input 48V Output Power Supply

- High efficiency Totem Pole CCM PFC + HF LLC
- $V_{in} = 90-265VAC$, $V_{out} = 48V$, $I_{out} = 21A$
- Full load efficiency: 92.5% & 95.4% @110 & 230VAC
- PCBA size: 328mm x 93mm x 50mm
- Power Density: 10.74W/in³
- Featuring products: TP PFC [NCP1681](#), LLC [NCP13994](#), iGaN [NCP58921](#), [NCP58920](#) & SR Controller [NCP4306](#)
- Application: Computing Power Supply, Industrial PSU

[Find Reference Design](#)




Figure 5: 1 kW 48V Output Power Supply Evaluation Board

Explore more power supply reference designs and evaluation boards from System Solution Guide - USB-C Battery Charger as below link.

Find more information in System Solution Guide:

USB-C Battery Charger

USB-C battery chargers have become the universal standard for quickly and effectively charging a wide range of portable devices, thanks to their high- power delivery and efficiency. The adoption of wide-bandgap semiconductors in these chargers further enhances efficiency, reduces energy losses, and contributes to the reduction in device size.



[Find System Solution Guide on the Web](#)

Switched-Mode Power Supply (SMPS)

Get Latest
Version

onsemi™

Intelligent Technology. Better Future.

Register now to unlock all System Solution Guides and get additional exclusive benefits!

- Join the conversation on community forum.
- Utilize Elite Power Simulator & other developer tools.
- Watch exclusive webinars and seminars.

Open full System Solution Guide



onsemi, the onsemi logo, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application, Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that onsemi was negligent regarding the design or manufacture of the part. onsemi is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.