



Title of Change:	NCN8025/A Datasheet update to align with EMV 4.3 standard		
Effective date:	4 October 2016		
Contact information:	Contact your local ON Semiconductor Sales Office or <Shannon.riggs@onsemi.com>		
Type of notification:	ON Semiconductor will consider this change accepted.		
Change category:	<input type="checkbox"/> Wafer Fab Change <input type="checkbox"/> Assembly Change <input type="checkbox"/> Test Change <input checked="" type="checkbox"/> Other Datasheet revision only		
Change Sub-Category(s):	<input type="checkbox"/> Manufacturing Site Change/Addition <input type="checkbox"/> Material Change <input checked="" type="checkbox"/> Datasheet/Product Doc change <input type="checkbox"/> Manufacturing Process Change <input type="checkbox"/> Product specific change <input type="checkbox"/> Shipping/Packaging/Marking <input type="checkbox"/> Other: _____		
Sites Affected:	<input type="checkbox"/> All site(s) <input checked="" type="checkbox"/> not applicable <input type="checkbox"/> ON Semiconductor site(s) : <input type="checkbox"/> External Foundry/Subcon site(s)		

Description and Purpose:

Datasheet NCN8025/D has been revised to align with the latest EMV standard, 4.3 (www.EMVco.com). For the affected devices, the Card I/O specifications (VOH, VOL, VIH, & VIL) have been revised in accordance with EMV 4.3, as shown below. The product characterization has been compared with the new standards and all parameters are capable to the new requirements. Manufacturing test programs have been revised and will be released effective W40, 2016 to ensure product adheres to the revised requirements.

The following changes have been made.

- CI/O VIH min @ 1.8 V mode changes from 1.2 V to 1.0 V
- CI/O VIL max @ 5.0 V mode changes from 0.8 V to 1.0 V
- CI/O VOH min changes from 0.75*CVCC to 0.8*CVCC
- CI/O VOL min @ 1.8 V mode changes from 0.3 V to 0.27 V

CAUX1, CAUX2, CI/O @ CVCC = 1.8 V, 3.0 V, 5.0 V					
VIH	Input Voltage High Level				
	1.8 V Mode	1.0	–	CVCC + 0.3	V
	3.0 V Mode	1.6	–	CVCC + 0.3	V
	5.0 V Mode	2.3	–	CVCC + 0.3	V
VIL	Input Voltage Low Level				
	1.8 V mode	–0.30	–	0.50	V
	3.0 V mode	–0.30	–	0.80	V
	5.0 V mode	–0.30		1.00	V
IIL	Low Level Input current VIL = 0 V	–		600	μA
	High Level Input current VIH = CVCC	–		10	μA
VOH	Output VOH				
	@ IOH = –40 μA for CVCC = 3.0 V and 5.0 V	0.8 * CVCC	–	CVCC + 0.1	V
	@ IOH = –20 μA for CVCC = 1.8 V	0.8 * CVCC	–	CVCC + 0.1	V
VOL	Output VOL				
	@ IOL = 1 mA, VIL = 0 V for CVCC = 1.8 V	0	–	0.27	V
	@ IOL = 1 mA, VIL = 0 V for CVCC = 3.0 V and 5.0 V	0		0.30	V
tRi / Fi	Input Rising/Falling times (Note 9)	–	–	1.2	μs
tRo / Fo	Output Rising/Falling times / COut = 80 pF (Note 9)	–	–	0.1	μs

This is a datasheet update to align with the EMV standard; there are NO product changes (die design or manufacturing BOM) occurring as a result of this change.



List of affected Standard Parts:

NCN8025AMNTXG
NCN8025MTTBG