

ON Semiconductor®

FDMS7658AS

N-Channel PowerTrench[®] SyncFETTM 30 V, 176 A, 1.9 m Ω

Features

- Max $r_{DS(on)}$ = 1.9 m Ω at V_{GS} = 10 V, I_D = 28 A
- Max $r_{DS(on)}$ = 2.2 m Ω at V_{GS} = 7 V, I_D = 26 A
- Advanced Package and Silicon Combination for Low r_{DS(on)} and High Efficiency
- SyncFETTM Schottky Body Diode
- MSL1 Robust Package Design
- 100% UIL Tested
- RoHS Compliant




General Description

The FDMS7658AS has been designed to minimize losses in power conversion application. Advancements in both silicon and package technologies have been combaton offer the lowest $r_{DS(on)}$ while maintaining excellent uching formance. This device has the added benefit of the pient much plithic Schottky body diode.

Applications

- Synchronour Rectific for L 'D' Converters
- Notebo、 Vcc 'GPU w Side Switch.
- 1 rking roine and Lory Side Switch

Tele m Se dary Side Rectification



MC TEI Via um Ratings TA = 25 °C unless otherwise noted.

Symbo	Parame ler			Ratings	Units
V _{D&}	Drain to Source Voltage			30	V
V _{GS}	Cate to Sourca Voltage		(Note 4)	±20	V
	Drain Current -Confinedus	T _C = 25 °C	(Note 5)	176	
. 0	Continuous	T _C = 100 °C	(Note 5)	112	Α
	Continuous	T _A = 25 °C	(Note 1a)	29	_ ^
3	-Pulsed		(Note 6)	670	
dv/dt	MOSFE1 dv/dt			1.5	V/ns
E _{AS}	Single Pulse Avalanche Energy		(Note 3)	162	mJ
P _D	Power Dissipation	T _C = 25 °C		89	W
	Power Dissipation	T _A = 25 °C	(Note 1a)	2.5	v
T _J , T _{STG}	Operating and Storage Junction Temperature R	ange		-55 to +150	°C

Thermal Characteristics

$R_{\theta JC}$	Thermal Resistance, Junction to Case	1.4	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient (Note 1a)	50	C/VV

Package Marking and Ordering Information

Device Marking	Device	Package	Reel Size	Tape Width	Quantity
FDMS7658AS	FDMS7658AS	Power 56	13 "	12 mm	3000 units

Electrical Characteristics $T_J = 25$ °C unless otherwise noted.

Symbol	Parameter	Test Conditions	Min.	Тур.	Max.	Units
Off Chara	cteristics					
BV_DSS	Drain to Source Breakdown Voltage	I _D = 1 mA, V _{GS} = 0 V	30			V
$\frac{\Delta BV_{DSS}}{\Delta T_J}$	Breakdown Voltage Temperature Coefficient	I _D = 10 mA, referenced to 25 °C		23		mV/°C
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = 24 V, V _{GS} = 0 V			500	μΑ
I _{GSS}	Gate to Source Leakage Current, Forward	$V_{GS} = 20 \text{ V}, V_{DS} = 0 \text{ V}$			100	nA

On Characteristics (Note 2)

V _{GS(th)}	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}$, $I_D = 1 \text{ mA}$	1.2	1.7	3.0	V
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate to Source Threshold Voltage Temperature Coefficient	I _D = 10 mA, referenced to 25 °C		-5		mV/°C
r _{DS(on)}	Static Drain to Source On Resistance	$V_{GS} = 10 \text{ V}, I_D = 28 \text{ A}$ $V_{GS} = 7 \text{ V}, I_D = 26 \text{ A}$ $V_{GS} = 4.5 \text{ V}, I_D = 23 \text{ A}$ $V_{GS} = 10 \text{ V}, I_D = 28 \text{ A}, T_J = 12 \text{ C}$		1.5	1.9 .2 2.4 2.6	- Msz
9 _{FS}	Forward Transconductance	$V_{GS} = 10 \text{ V}, I_D = 28 \text{ A}$ $V_{DS} = 5 \text{ V}, I_D = 28 \text{ A}$		181	110	S

Dynamic Characteristics

C _{iss}	Input Capacitance	V 45				5525	7350	pF
C _{oss}	Output Capacitance	$V_{DS} = 15$ V $f = 1$ Hz	G = U		1.0	2020	2685	pF
C _{rss}	Reverse Transfer Capacitance	112				50	250	pF
R_g	Gate Resistance			70	0.1	0.4	υ9	Ω

Switching Characteristics


t _{d(on)}	Turn-On Delay Time	<u> </u>	20	36	ns
t _r	Rise Time $V_{DD} = 15 \text{ V}_{1D} = 28 \text{ A},$) (<u>vo</u>	8	17	ns
t _{d(off)}	Turn-Off Delay Time $V_{CS} = 0.0$ V, $R_{SEN} = 3.0$	11/1	43	70	ns
t _f	Fall Time		5	10	ns
Qg	Total Gate C rge V _{GS} = 0.110 V		78	109	nC
Q_g	To' Gale Ch. 9 $V_{CS} = 0 \text{ V to 4.5 V}_{DD} =$	= 15 V,	35	49	nC
Q _{gs}	G e Gaue Charge I _D = 2	8 A	16.4		nC
Q _{gd}	Fate to Dra 'Miller" Charge		6.6		nC

ain-S. rc. Diode Characteristics

V _{SD} Source to Drain Digite: Forward Voltage	$V_{GS} = 0 \text{ V}, I_S = 2 \text{ A}$ (Note 2)	0.38	0.9	V
V _{SD} Source to Drain Diode Forward Voltage	$V_{GS} = 0 \text{ V}, I_S = 28 \text{ A}$ (Note 2)	0.74	1.3	v
t _{rr} Reverse Recovery Time	I _E = 28 A. di/dt = 300 A/us	46	75	ns
Q _{rr} Reverse Recovery Charge	IF - 26 A, αι/αι - 300 Α/μs	73	117	nC

Notes:

Reva is determined with the device reported on a 1in² pad 2 oz copper pad on a 1.5 x 1.5 in. board of FR-4 material. Reva is guaranteed by design while Reca is determined by the user's board design.



a. 50 °C/W when mounted on a 1 in² pad of 2 oz copper.



b. 125 °C/W when mounted on a minimum pad of 2 oz copper.

- 2. Pulse Test: Pulse Width < 300 μ s, Duty cycle < 2.0%. 3. E_{AS} of 162 mJ is based on starting T_J = 25 °C, L = 1 mH, I_{AS} = 18 A, V_{DD} = 27 V, V_{GS} = 10 V. 100% test at L = 0.3 mH, I_{AS} = 28 A. 4. As an N-ch device, the negative Vgs rating is for low duty cycle pulse occurrence only. No continuous rating is implied. 5. Computed continuous current limited to Max Junction Temperature only, actual continuous current will be limited by thermal & electro-mechanical application board design. 6. Pulsed Id please refer to Fig 11 SOA graph for more details.

Typical Characteristics T_J = 25 °C unless otherwise noted.




Figure 1. On-Region Characteristics




Fig. resolverm ized On-Resistance vs. 'ur aon Temperature




Figure 5. Transfer Characteristics




Figure 2. rm. ad On Resistance vs. Prain rre. ar sate Voltage




Figure 4. On-Resistance vs. Gate to Source Voltage




Figure 6. Source to Drain Diode Forward Voltage vs. Source Current

Typical Characteristics $T_J = 25$ °C unless otherwise noted.




Figure 7. Gate Charge Characteristics




Fig. J. UI lampedInductive




Figure 11. Forward Bias Safe Operating Area




Figure Cal ancevs. Jrain to Sou a V age




Figure 10. Maximum Continuous Drain Current vs. Case Temperature




Figure 12. Single Pulse Maximum Power Dissipation






Figure 13. Junction-to-Case Transient Thermal Resp. se ry

Typical Characteristics (continued)

SyncFETTM Schottky body diode Characteristics

ON Semiconductor's SyncFETTM process embeds a Schottky diode in parallel with PowerTrench MoSFET. This diode exhibits similar characteristics to a discrete external Schottky diode in parallel with a MOSFET. Figure 14 shows the reverses recovery characteristic of the FDMS7658AS.

Schottky barrier diodes exhibit significant leakage at high temperature and high reverse voltage. This will increase the power in the device.




Figure 14. FDMS7658AS Sv TM Didy Diode Reverse Recovery (paracte Stic




Figure 15. SyncFFTT Body Diode Reverses Leakage vs. Drain-Source Voltage



ON Semiconductor and III) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns me rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdt/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages.

Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada

Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative