

Thank you for your interest in **onsemi** products.
Your technical document begins on the following pages.



Your Feedback is Important to Us!

Please take a moment to participate in our short survey.
At **onsemi**, we are dedicated to delivering technical content that best meets your needs.

[Help Us Improve – Take the Survey](#)

This survey is intended to collect your feedback, capture any issues you may encounter, and to provide improvements you would like to suggest.

We look forward to your feedback.

To learn more about **onsemi**, please visit our website at
www.onsemi.com

onsemi and **onsemi** and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi** product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner. Other names and brands may be claimed as the property of others.

Silicon Carbide (SiC) Module – EliteSiC, 3 m Ω SiC M3 MOSFET, 1200 V, 2-PACK Half Bridge Topology, F2 Package with HPS DBC

NXH003P120M3F2PTHG

The NXH003P120M3F2PTHG is a power module containing 3 m Ω / 1200 V SiC MOSFET half-bridge and a thermistor with HPS DBC in an F2 package.

Features

- 3 m Ω / 1200 V M3S SiC MOSFET Half-Bridge
- HPS DBC
- Thermistor
- Pre-Applied Thermal Interface Material (TIM)
- Press-Fit Pins
- These Devices are Pb-Free, Halide Free and are RoHS Compliant

Typical Applications

- Solar Inverter
- Uninterruptible Power Supplies
- Electric Vehicle Charging Stations
- Industrial Power






Figure 1. NXH003P120M3F2 Schematic Diagram

PACKAGE PICTURE




PIM36 56.7x42.5 (PRESS FIT)
CASE 180BY

MARKING DIAGRAM



NXH003P120M3F2PTHG = Specific Device Code
AT = Assembly & Test Site Code
YYWW = Year and Work Week Code

PIN CONNECTIONS



See Pin Function Description for pin names

ORDERING INFORMATION

See detailed ordering and shipping information on page 4 of this data sheet.

NXH003P120M3F2PTHG

PIN FUNCTION DESCRIPTION

| Pin | Name | Description |
|-----|-------|--------------------------------------|
| 1 | S1 | Q1 Kelvin Emitter (High side switch) |
| 2 | G1 | Q1 Gate (High side switch) |
| 3 | G1 | Q1 Gate (High side switch) |
| 4 | S1 | Q1 Kelvin Emitter (High side switch) |
| 5 | DC+ | DC Positive Bus connection |
| 6 | DC+ | DC Positive Bus connection |
| 7 | DC+ | DC Positive Bus connection |
| 8 | DC+ | DC Positive Bus connection |
| 9 | DC+ | DC Positive Bus connection |
| 10 | DC+ | DC Positive Bus connection |
| 11 | DC+ | DC Positive Bus connection |
| 12 | DC+ | DC Positive Bus connection |
| 13 | DC* | DC Negative Bus connection |
| 14 | DC- | DC Negative Bus connection |
| 15 | DC- | DC Negative Bus connection |
| 16 | DC- | DC Negative Bus connection |
| 17 | DC- | DC Negative Bus connection |
| 18 | DC- | DC Negative Bus connection |
| 19 | DC- | DC Negative Bus connection |
| 20 | DC- | DC Negative Bus connection |
| 21 | PHASE | Center point of half bridge |
| 22 | PHASE | Center point of half bridge |
| 23 | PHASE | Center point of half bridge |
| 24 | PHASE | Center point of half bridge |
| 25 | PHASE | Center point of half bridge |
| 26 | S2 | Q2 Kelvin Emitter (Low side switch) |
| 27 | G2 | Q2 Gate (Low side switch) |
| 28 | TH1 | Thermistor Connection 1 |
| 29 | TH2 | Thermistor Connection 2 |
| 30 | S2 | Q2 Kelvin Emitter (Low side switch) |
| 31 | G2 | Q2 Gate (Low side switch) |
| 32 | PHASE | Center point of half bridge |
| 33 | PHASE | Center point of half bridge |
| 34 | PHASE | Center point of half bridge |
| 35 | PHASE | Center point of half bridge |
| 36 | PHASE | Center point of half bridge |

NXH003P120M3F2PTHG

MAXIMUM RATINGS

| Rating | Symbol | Value | Unit |
|--|--------------|---------|------------------|
| SiC MOSFET | | | |
| Drain–Source Voltage | V_{DSS} | 1200 | V |
| Gate–Source Voltage | V_{GS} | +22/-10 | V |
| Continuous Drain Current @ $T_c = 80^\circ\text{C}$ ($T_J = 175^\circ\text{C}$) | I_D | 350 | A |
| Pulsed Drain Current ($T_J = 175^\circ\text{C}$) | I_{Dpulse} | 700 | A |
| Maximum Power Dissipation @ $T_c = 80^\circ\text{C}$ ($T_J = 175^\circ\text{C}$) | P_{tot} | 979 | W |
| Minimum Operating Junction Temperature | T_{JMIN} | -40 | $^\circ\text{C}$ |
| Maximum Operating Junction Temperature | T_{JMAX} | 175 | $^\circ\text{C}$ |

THERMAL PROPERTIES

| | | | |
|---------------------------|-----------|--------------|------------------|
| Storage Temperature Range | T_{stg} | -40 to 150 | $^\circ\text{C}$ |
| TIM Layer Thickness | T_{TIM} | 160 \pm 20 | μm |

INSULATION PROPERTIES

| | | | |
|--|----------|----------|-----------|
| Isolation Test Voltage, $t = 1$ s, 60 Hz | V_{is} | 4800 | V_{RMS} |
| Creepage Distance | | 12.7 | mm |
| CTI | | 600 | |
| Substrate Ceramic Material | | HPS | |
| Substrate Ceramic Material Thickness | | 0.38 | mm |
| Substrate Warpage (Note 2) | W | Max 0.18 | mm |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Refer to ELECTRICAL CHARACTERISTICS, RECOMMENDED OPERATING RANGES and/or APPLICATION INFORMATION for Safe Operating parameters.
2. Height difference between horizontal plane and substrate copper bottom.

RECOMMENDED OPERATING RANGES

| Rating | Symbol | Min | Max | Unit |
|---------------------------------------|--------|-----|-----|------------------|
| Module Operating Junction Temperature | T_J | -40 | 150 | $^\circ\text{C}$ |

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended Operating Ranges limits may affect device reliability.

ELECTRICAL CHARACTERISTICS ($T_J = 25^\circ\text{C}$ unless otherwise noted)

| Parameter | Test Conditions | Symbol | Min | Typ | Max | Unit |
|-----------------------------------|---|--------------|------|-------|-----|------------------|
| SiC MOSFET CHARACTERISTICS | | | | | | |
| Zero Gate Voltage Drain Current | $V_{GS} = 0$ V, $V_{DS} = 1200$ V | I_{DSS} | - | - | 300 | μA |
| Drain–Source On Resistance | $V_{GS} = 18$ V, $I_D = 200$ A, $T_J = 25^\circ\text{C}$ | $R_{DS(ON)}$ | - | 3.19 | 5 | $\text{m}\Omega$ |
| | $V_{GS} = 18$ V, $I_D = 200$ A, $T_J = 125^\circ\text{C}$ | | - | 5.25 | - | |
| | $V_{GS} = 18$ V, $I_D = 200$ A, $T_J = 150^\circ\text{C}$ | | - | 5.88 | - | |
| Gate–Source Threshold Voltage | $V_{GS} = V_{DS}$, $I_D = 160$ mA | $V_{GS(TH)}$ | 1.8 | 2.4 | 4.4 | V |
| Gate Leakage Current | $V_{GS} = -10$ V / 20 V, $V_{DS} = 0$ V | I_{GSS} | -800 | - | 800 | nA |
| Input Capacitance | $V_{DS} = 800$ V, $V_{GS} = 0$ V, $f = 100$ kHz | C_{ISS} | - | 20889 | - | pF |
| Reverse Transfer Capacitance | | C_{RSS} | - | 90 | - | |
| Output Capacitance | | C_{OSS} | - | 1225 | - | |

NXH003P120M3F2PTHG

ELECTRICAL CHARACTERISTICS ($T_J = 25^\circ\text{C}$ unless otherwise noted) (continued)

| Parameter | Test Conditions | Symbol | Min | Typ | Max | Unit |
|---------------------------------------|---|----------------|-----|-------|-----|---------------------------|
| SiC MOSFET CHARACTERISTICS | | | | | | |
| Total Gate Charge | $V_{DS} = 800\text{ V}, V_{GS} = -5/20\text{ V}, I_D = 200\text{ A}$ | $Q_{G(TOTAL)}$ | – | 1195 | – | nC |
| Gate–Source Charge | | Q_{GS} | – | 232 | – | nC |
| Gate–Drain Charge | | Q_{GD} | – | 210 | – | nC |
| Turn-on Delay Time | $T_J = 25^\circ\text{C}$ $V_{DS} = 600\text{ V}, I_D = 200\text{ A}$ $V_{GS} = -5\text{ V} / 18\text{ V}, R_G = 1\ \Omega$ | $t_{d(on)}$ | – | 49 | – | ns |
| Rise Time | | t_r | – | 17 | – | |
| Turn-off Delay Time | | $t_{d(off)}$ | – | 144 | – | |
| Fall Time | | t_f | – | 16 | – | |
| Turn-on Switching Loss per Pulse | | E_{ON} | – | 1.79 | – | mJ |
| Turn-off Switching Loss per Pulse | | E_{OFF} | – | 1.13 | – | |
| Turn-on Delay Time | $T_J = 150^\circ\text{C}$ $V_{DS} = 600\text{ V}, I_D = 200\text{ A}$ $V_{GS} = -5\text{ V} / 18\text{ V}, R_G = 1\ \Omega$ | $t_{d(on)}$ | – | 48 | – | ns |
| Rise Time | | t_r | – | 15 | – | |
| Turn-off Delay Time | | $t_{d(off)}$ | – | 154 | – | |
| Fall Time | | t_f | – | 15 | – | |
| Turn-on Switching Loss per Pulse | | E_{ON} | – | 1.94 | – | mJ |
| Turn off Switching Loss per Pulse | | E_{OFF} | – | 1.12 | – | |
| Diode Forward Voltage | $I_D = 200\text{ A}, T_J = 25^\circ\text{C}$ | V_{SD} | – | 4.8 | 7.5 | V |
| | $I_D = 200\text{ A}, T_J = 125^\circ\text{C}$ | | – | 4.5 | – | |
| | $I_D = 200\text{ A}, T_J = 150^\circ\text{C}$ | | – | 4.4 | – | |
| Thermal Resistance – Chip-to–Case | M1, M2 | R_{thJC} | – | 0.097 | – | $^\circ\text{C}/\text{W}$ |
| Thermal Resistance – Chip-to–Heatsink | Thermal grease, Thickness = 2 Mil +2%, $A = 2.8\text{ W}/\text{mK}$ | R_{thJH} | – | 0.202 | – | $^\circ\text{C}/\text{W}$ |

THERMISTOR CHARACTERISTICS

| | | | | | | |
|---------------------------------------|----------------------------------|--------------|----|-------|---|------------|
| Nominal Resistance | $T_{NTC} = 25^\circ\text{C}$ | R_{25} | – | 5 | – | k Ω |
| | $T_{NTC} = 100^\circ\text{C}$ | R_{100} | – | 493 | – | Ω |
| | $T_{NTC} = 150^\circ\text{C}$ | R_{150} | – | 159.5 | – | Ω |
| Deviation of R_{100} | $T_{NTC} = 100^\circ\text{C}$ | $\Delta R/R$ | –5 | – | 5 | % |
| Power Dissipation – Recommended Limit | 0.15 mA, Non–self–heating Effect | P_D | – | 0.1 | – | mW |
| Power Dissipation – Absolute Maximum | 5 mA | P_D | – | 34.2 | – | mW |
| Power Dissipation Constant | | | – | 1.4 | – | mW/K |
| B–value | B (25/50), Tolerance $\pm 2\%$ | | – | 3375 | – | K |
| B–value | B (25/100), Tolerance $\pm 2\%$ | | – | 3436 | – | K |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

ORDERING INFORMATION

| Orderable Part Number | Marking | Package | Shipping |
|-----------------------|--------------------|--|-------------------------|
| NXH003P120M3F2PTHG | NXH003P120M3F2PTHG | F2HALFBR: Case 180BY Press-fit Pins with pre-applied thermal interface material (TIM) (Pb-Free / Halide Free) | 20 Units / Blister Tray |

NXH003P120M3F2PTHG

TYPICAL CHARACTERISTIC (M1/M2 SiC MOSFET CHARACTERISTIC)




Figure 2. MOSFET Typical Output Characteristic




Figure 3. MOSFET Typical Output Characteristic




Figure 4. MOSFET Typical Transfer Characteristic




Figure 5. Body Diode Forward Characteristic

NXH003P120M3F2PTHG

TYPICAL CHARACTERISTIC (M1/M2 SiC MOSFET CHARACTERISTIC)




Figure 6. Gate-to-Source Voltage vs. Total Charge




Figure 7. Capacitance vs. Drain-to-Source Voltage

NXH003P120M3F2PTHG

TYPICAL CHARACTERISTIC (M1/M1 SiC MOSFET SWITCHING CHARACTERISTIC)




Figure 8. Typical Switching Loss Eon vs. ID




Figure 9. Typical Switching Loss Eon vs. Rg




Figure 10. Typical Switching Loss Eoff vs. ID




Figure 11. Typical Switching Loss Eoff vs. Rg




Figure 12. Typical Switching Loss Tdon vs. ID




Figure 13. Typical Switching Loss Tdon vs. Rg

NXH003P120M3F2PTHG

TYPICAL CHARACTERISTIC (M1/M1 SiC MOSFET SWITCHING CHARACTERISTIC)




Figure 14. Typical Switching Loss Tdoff vs. ID




Figure 15. Typical Switching Loss Tdoff vs. Rg




Figure 16. Typical Switching Loss Tr vs. ID




Figure 17. Typical Switching Loss Tr vs. Rg




Figure 18. Typical Switching Loss Tf vs. ID




Figure 19. Typical Switching Loss Tf vs. Rg

TYPICAL CHARACTERISTIC
(M1/M1 SiC MOSFET SWITCHING CHARACTERISTIC)




Figure 20. di/dt ON vs. ID




Figure 21. di/dt ON vs. RG




Figure 22. di/dt OFF vs. ID




Figure 23. di/dt OFF vs. RG




Figure 24. dv/dt ON vs. ID




Figure 25. dv/dt ON vs. RG

NXH003P120M3F2PTHG

TYPICAL CHARACTERISTIC (M1/M1 SiC MOSFET SWITCHING CHARACTERISTIC)




Figure 26. dv/dt OFF vs. I_D




Figure 27. dv/dt OFF vs. R_G

NXH003P120M3F2PTHG

TYPICAL CHARACTERISTIC (M1/M1 SiC MOSFET CHARACTERISTIC)





Figure 28. MOSFET Junction-to-Case Transient Thermal Impedance

Table 1. FOSTER NETWORKS – M1, M2

| Foster Element # | M1 | | M2 | |
|------------------|-------------|-------------|-------------|-------------|
| | Rth (K/W) | Cth (Ws/K) | Rth (K/W) | Cth (Ws/K) |
| 1 | 0.002119710 | 0.006269327 | 0.002085717 | 0.005919216 |
| 2 | 0.002237509 | 0.044417021 | 0.002262963 | 0.041549892 |
| 3 | 0.010754082 | 0.080568359 | 0.011217723 | 0.075947544 |
| 4 | 0.012973790 | 0.473570059 | 0.013624461 | 0.468022154 |
| 5 | 0.071830979 | 0.438172158 | 0.07157749 | 0.444577769 |


Table 2. CAUER NETWORKS – M1, M2

| Cauer Element # | M1 | | M2 | |
|-----------------|-------------|-------------|-------------|-------------|
| | Rth (K/W) | Cth (Ws/K) | Rth (K/W) | Cth (Ws/K) |
| 1 | 0.003228661 | 0.005029516 | 0.003176874 | 0.004749202 |
| 2 | 0.005914795 | 0.025033712 | 0.005878559 | 0.023599253 |
| 3 | 0.015486364 | 0.043255417 | 0.015761478 | 0.041433746 |
| 4 | 0.041123543 | 0.201827107 | 0.04214085 | 0.20355778 |
| 5 | 0.034162706 | 0.484541759 | 0.033810593 | 0.506186577 |



PIM36 56.70x42.50x12.00
CASE 180BY
ISSUE E



DATE 20 DEC 2023




NOTES:

1. CONTROLLING DIMENSION: MILLIMETERS
2. PIN POSITION TOLERANCE IS $\pm 0.4\text{mm}$
3. PRESS FIT PIN


| DIM | MILLIMETERS | | |
|-----|-------------|-------|-------|
| | MIN. | NOM. | MAX. |
| A | 11.65 | 12.00 | 12.35 |
| A1 | 16.10 | 16.50 | 16.90 |
| A2 | 0.00 | 0.35 | 0.60 |
| A3 | 12.95 | 13.35 | 13.75 |
| b | 1.15 | 1.20 | 1.25 |
| b1 | 0.59 | 0.64 | 0.69 |
| D | 56.40 | 56.70 | 57.00 |
| D1 | 4.40 | 4.50 | 4.60 |
| D2 | 50.85 | 51.00 | 51.15 |
| E | 47.70 | 48.00 | 48.30 |
| E1 | 42.35 | 42.50 | 42.65 |
| E2 | 52.90 | 53.00 | 53.10 |
| E3 | 62.30 | 62.80 | 63.30 |
| E4 | 4.90 | 5.00 | 5.10 |
| P | 2.20 | 2.30 | 2.40 |



GENERIC
MARKING DIAGRAM*



FRONTSIDE MARKING



BACKSIDE MARKING

XXXXX = Specific Device Code
AT = Assembly & Test Site Code
YYWW = Year and Work Week Code

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "▪", may or may not be present. Some products may not follow the Generic Marking.

| | | |
|------------------|-------------------------|--|
| DOCUMENT NUMBER: | 98AON19725H | Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| DESCRIPTION: | PIM36 56.70x42.50x12.00 | PAGE 1 OF 1 |

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales