ON Semiconductor

Is Now



To learn more about onsemi™, please visit our website at www.onsemi.com

onsemi and ONSEMI. and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use onsemi products for any such unintended or unauthorized application,

MOSFET - PowerTrench® Power Clip, Asymmetric, Dual N-Channel 30 V



General Description

This device includes two specialized N-Channel MOSFETs in a dual package. The switch node has been internally connected to enable easy placement and routing of synchronous buck converters. The control MOSFET (Q1) and synchronous SyncFET (Q2) have been designed to provide optimal power efficiency.

Features

Q1: N-Channel

- Max $r_{DS(on)} = 5.0 \text{ m}\Omega$ at $V_{GS} = 10 \text{ V}$, ID = 17 A
- Max $r_{DS(on)}$ = 6.5 m Ω at V_{GS} = 4.5 V, ID = 14 A Q2: N-Channel
- Max $r_{DS(on)} = 1.6 \text{ m}\Omega$ at $V_{GS} = 10 \text{ V}$, ID = 32 A
- Max $r_{DS(on)} = 2.0 \text{ m}\Omega$ at $V_{GS} = 4.5 \text{ V}$, ID = 28 A
- Low Inductance Packaging Shortens Rise/Fall Times, Resulting in Lower Switching Losses
- MOSFET Integration Enables Optimum Layout for Lower Circuit Inductance and Reduced Switch Node Ringing
- These Devices are Pb–Free, Halogen Free/BFR Free and are RoHS Compliant

Applications


- Computing
- Communications
- General Purpose Point of Load

Pin	Name	Description		
1	HSG	High Side Gate		
2	GR	Gate Return		
3, 4, 9	V+(HSD)	High Side Drain		
5, 6, 7	SW	Switching Node, Low Side Drain		
8	LSG	Low Side Gate		
10	GND(LSS)	Low Side Source		





ON Semiconductor®

www.onsemi.com









ORDERING INFORMATION


See detailed ordering and shipping information on page 3 of this data sheet

Table 1. MOSFET MAXIMUM RATINGS $T_A = 25^{\circ}C$ unless otherwise noted.


Symbol	Parameter		Q1	Q2	Units
V _{DS}	Drain to Source Voltage		30	30	V
B _{VDDST}	B _{VDDST} (transient) < 100 ns		32.5	32.5	V
V_{GS}	Gate to Source Voltage		±20	±12	V
I _D	Drain Current -Continuous	T _C = 25°C (Note 1)	56	109	Α
	- Continuous	T _C = 100°C (Note 1)	35	69	
	- Continuous	T _A = 25°C	17 (Note 4)	32 (Note 5)	
	- Pulsed	T _A = 25°C (Note 2)	227	704	
E _{AS}	Single Pulse Avalanche Energy	(Note 3)	54	181	mJ
P_{D}	Power Dissipation for Single Operation	T _C = 25°C	23	29	W
	Power Dissipation for Single Operation	T _A = 25°C	2.1 (Note 4)	2.3 (Note 5)	
	Power Dissipation for Single Operation	T _A = 25°C	1.0 (Note 6)	1.1 (Note 7)	
T_J , T_{STG}	Operating and Storage Junction Temperature Range		–55 to	+150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.


- 1. Computed continuous current limited to Max Junction Temperature only, actual continuous current will be limited by thermal & electro-mechanical application board design.
- Pulsed Id refer to Figure 11 and Figure 24 SOA curve for more details.
 Q1 :EAS of 54 mJ is based on starting T_J = 25°C; L = 3 mH, I_{AS} = 6 A, V_{DD} = 30 V, V_{GS} = 10 V. 100% tested at L = 0.1 mH, I_{AS} =20 A. Q2: EAS of 181 mJ is based on starting T_J = 25°C; L = 3 mH, I_{AS} = 11 A, V_{DD} = 30 V, V_{GS} = 10 V. 100% tested at L = 0.1 mH, I_{AS} =36 A.




4. 60° C/W when mounted on a 1 in² pad of 2 oz copper



5. 55°C/W when mounted on a 1 in² pad of 2 oz copper



6. 130°C/W when mounted on a 1 in² pad of 2 oz copper



7. 120°C/W when mounted on a 1 in² pad of 2 oz copper

Table 2. PACKAGE MARKING AND ORDERING INFORMATION

Device Marking	Device	Package	Reel Size	Tape Width	Quantity
D1D6	NTMFD1D6N03P8	Power Clip 56	13″	12 mm	3000 units

Table 3. THERMAL CHARACTERISTICS

$R_{ heta JC}$	Thermal Resistance, Junction to Case	5.6	4.3	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	60 (Note 8)	55 (Note 8)	
$R_{ heta JA}$	Thermal Resistance, Junction to Ambient	130 (Note 8)	120 (Note 8)	

R_{θJA} is determined with the device mounted on a 1 in² pad 2 oz copper pad on a 1.5 x 1.5 in. board of FR-4 material, R_{θCA} is determined by the user's board design.

Table 4. ELECTRICAL CHARACTERISTICS $T_J = 25^{\circ}C$ unless otherwise noted.

Symbol	Parameter	Test Conditions	Туре	Min	Тур	Max	Units
OFF CHAR	ACTERISTICS	•		•		•	•
BV _{DSS}	Drain to Source Breakdown Voltage	$\begin{split} I_D &= 250 \; \mu\text{A}, V_{GS} = 0 \; \text{V} \\ I_D &= 1 \; \text{mA}, V_{GS} = 0 \; \text{V} \end{split}$	Q1 Q2	30 30			V
$\Delta BV_{DSS/} \over \Delta T_{J}$	Breakdown Voltage Temperature Coefficient	I_D = 250 μ A, referenced to 25°C I_D = 10 mA, referenced to 25°C	Q1 Q2		15 19		mV/°C
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = 24 V, V _{GS} = 0 V V _{DS} = 24 V, V _{GS} = 0 V	Q1 Q2			1 500	μ Α μ Α
I _{GSS}	Gate to Source Leakage Current, Forward	V _{GS} = 20 V, V _{DS} = 0 V V _{GS} = 12 V, V _{DS} = 0 V	Q1 Q2			100 100	nA nA
ON CHARA	CTERISTICS						
V _{GS(th)}	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}, I_D = 250 \mu A$ $V_{GS} = V_{DS}, I_D = 1 \text{ mA}$	Q1 Q2	1.0 1.0	1.7 1.6	3.0 3.0	V
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate to Source Threshold Voltage Temperature Coefficient	I_D = 250 μ A, referenced to 25°C I_D = 10 mA, referenced to 25°C	Q1 Q2		-5 -3		mV/°C
r _{DS(on)}	Drain to Source On Resistance	$V_{GS} = 10 \text{ V}, I_D = 17 \text{ A}$ $V_{GS} = 4.5 \text{ V}, I_D = 14 \text{ A}$ $V_{GS} = 10 \text{ V}, I_D = 17 \text{ A}, T_J = 125^{\circ}\text{C}$	Q1		4.1 5.4 5.7	5.0 6.5 7.0	mΩ
		V_{GS} = 10 V, I_{D} = 32 A V_{GS} = 4.5 V, I_{D} = 28 A V_{GS} = 10 V, I_{D} = 32 A, T_{J} = 125°C	Q2		1.4 1.7 2.1	1.6 2.0 2.4	
9FS	Forward Transconductance	V _{DS} = 5 V, I _D = 17 A V _{DS} = 5 V, I _D = 32 A	Q1 Q2		93 188		S
DYNAMIC (CHARACTERISTICS	•					
C _{iss}	Input Capacitance	Q1: V _{DS} = 15 V, V _{GS} = 0 V, f = 1 MHZ	Q1 Q2		1224 4593	1715 6430	pF
C _{oss}	Output Capacitance	Q2:	Q1 Q2		397 1210	560 1695	pF
C_{rss}	Reverse Transfer Capacitance	V _{DS} = 15 V, V _{GS} = 0 V, f = 1 MHZ	Q1 Q2		42 80	60 115	pF
R_g	Gate Resistance		Q1 Q2	0.1 0.1	0.5 0.8	1.5 2.4	Ω
SWITCHING	CHARACTERISTICS						
t _{d(on)}	Turn-On Delay Time	Q1: V _{DD} = 15 V, I _D = 17 A, R _{GEN} = 6 Ω	Q1 Q2		8 14	16 25	ns
t _r	Rise Time	Q2:	Q1 Q2		2 5	10 10	ns
t _{d(off)}	Turn-Off Delay Time	V_{DD} = 15 V, I_{D} = 32 A, R_{GEN} = 6 Ω	Q1 Q2		18 38	33 61	ns
t _f	Fall Time	7	Q1 Q2		2 4	10 10	ns

Table 4. ELECTRICAL CHARACTERISTICS T. = 25°C unless otherwise noted.

Table 4. ELECTRICAL CHARACTERISTICS Ty = 25°C unless otherwise noted.									
Symbol	Parameter	Test Cor	nditions	Type	Min	Тур	Max	Units	
SWITCHING CHARACTERISTICS									
Qg	Total Gate Charge	V _{GS} = 0 V to 10 V	Q1 V _{DD} = 15 V,	Q1 Q2		17 62	24 87	nC	
Qg	Total Gate Charge	V _{GS} = 0 V to 4.5 V	I _D = 17 A	Q1 Q2		8 28	11 40	nC	
Q_{gs}	Gate to Source Gate Charge		V _{DD} = 15 V, I _D = 32 A	Q1 Q2		3.1 11		nC	
Q _{gd}	Gate to Drain "Miller" Charge			Q1 Q2		2.0 5.3		nC	
DRAIN-SOL	JRCE DIODE CHARACTERISTICS								
V_{SD}	Source to Drain Diode Forward Voltage	V _{GS} = 0 V, I _S = 17 A (Note 9) V _{GS} = 0 V, I _S = 32 A (Note 9)		Q1 Q2		0.8 0.8	1.2 1.2	V	
t _{rr}	Reverse Recovery Time	Q1 I _F = 17 A, di/dt = 100) A/μs	Q1 Q2		23 32	37 51	ns	
Q_{rr}	Reverse Recovery Charge	Q2 I _F = 32 A, di/dt = 240) A/μs	Q1 Q2		8 40	16 64	nC	

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

9. Pulse Test: Pulse Width < 300 µs, Duty Cycle < 2.0%.

Typical Characteristics (Q1 N–Channel) $T_J = 25$ °C unless otherwise noted.




Figure 1. On Region Characteristics




Figure 3. Normalized On–Resistance vs. Junction Temperature




Figure 5. Transfer Characteristics




Figure 2. Normalized On–Resistance vs. Drain Current and Gate Voltage




Figure 4. On-Resistance vs. Gate to Source Voltage




Figure 6. Source to Drain Diode Forward Voltage vs. Source Current

Typical Characteristics (Q1 N-Channel) T_J = 25°C unless otherwise noted.




Figure 7. Gate Charge Characteristics




Figure 9. Unclamped Inductive Switching Capability




Figure 11. Forward Bias Safe Operating

Area




Figure 8. Capacitance vs. Drain to Source Voltage




Figure 10. Maximum Continuous Drain Current vs. Case Temperature




Figure 12. Single Pulse Maximum Power Dissipation

Typical Characteristics (Q1 N–Channel) $T_J = 25^{\circ}C$ unless otherwise noted.




Figure 13. Junction-to-Case Transient Thermal Response Curve

Typical Characteristics (Q2 N–Channel) $T_J = 25$ °C unless otherwise noted.




Figure 14. On Region Characteristics




Figure 16. Normalized On–Resistance vs. Junction Temperature




Figure 18. Transfer Characteristics




Figure 15. Normalized On-Resistance vs. Drain Current and Gate Voltage




Figure 17. On–Resistance vs. Gate to Source Voltage




Figure 19. Source to Drain Diode Forward Voltage vs. Source Current

Typical Characteristics (Q2 N-Channel) T_J = 25°C unless otherwise noted.




Figure 20. Gate Charge Characteristics




Figure 22. Unclamped Inductive Switching Capability




Figure 24. Forward Bias Safe Operating Area




Figure 21. Capacitance vs. Drain to Source Voltage




Figure 23. Maximum Continuous Drain Current vs. Case Temperature




Figure 25. Single Pulse Maximum Power Dissipation

Typical Characteristics (Q2 N-Channel) T_J = 25°C unless otherwise noted.




Figure 26. Junction-to-Case Transient Thermal Response Curve

Typical Characteristics

SyncFET Schottky Body Diode Characteristics

ON Semiconductor's SyncFET process embeds a Schottky diode in parallel with PowerTrench MOSFET. This diode exhibits similar characteristics to a discrete external Schottky diode in parallel with a MOSFET. Figure 27 shows the reverse recovery characteristic of the FDPC5018SG.

Schottky barrier diodes exhibit significant leakage at high temperature and high reverse voltage. This will increase the power in the device.




Figure 27. SyncFET Body Diode Reverse Recovery Characteristic





Figure 28. SyncFET Body Diode Reverse Leakage vs. Drain-Source Voltage

PACKAGE DIMENSIONS



PowerTrench is a registered trademark of Semiconductor Components Industries, LLC.

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor datas sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify a

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303–675–2175 or 800–344–3860 Toll Free USA/Canada Fax: 303–675–2176 or 800–344–3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative