

# ON Semiconductor

## Is Now

The logo for onsemi, featuring the word "onsemi" in a dark teal, lowercase, sans-serif font. The letter "i" is stylized with a white dot and a teal vertical bar. A small orange triangle is positioned above the top right of the "i". A trademark symbol (TM) is located to the right of the logo.

To learn more about onsemi™, please visit our website at  
[www.onsemi.com](http://www.onsemi.com)

---

**onsemi** and **onsemi** and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi** product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner. Other names and brands may be claimed as the property of others.



**ON Semiconductor®**



# **200 W Game Console AC-DC Adapter**

## **Reference Design Documentation Package**

Disclaimer: ON Semiconductor is providing this reference design documentation package “AS IS” and the recipient assumes all risk associated with the use and/or commercialization of this design package. No licenses to ON Semiconductor’s or any third party’s Intellectual Property is conveyed by the transfer of this documentation. This reference design documentation package is provided only to assist the customers in evaluation and feasibility assessment of the reference design. It is expected that users may make further refinements to meet specific performance goals.

# TND331

## 200 W Game Console AC-DC Adapter

### Reference Design Documentation Package



ON Semiconductor®

<http://onsemi.com>

### TECHNICAL NOTE

#### OVERVIEW

This reference document describes a built-and-tested, GreenPoint™ solution for a Game Console AC-DC adapter.


The reference design is targeted for the XBOX® Game Console from Microsoft®. The block diagram of the architecture used in this reference design is shown in Figure 1.

As seen in the figure, this reference design employs an Active Clamp Forward topology for the main converter. A new, highly integrated active clamp controller IC from ON Semiconductor - NCP1562 - was used for this main converter. This eased the implementation due to the many features that are integrated, thereby reducing the overall system cost and number of components while achieving the higher efficiency targeted for this reference design.

This reference design also includes a 5 V standby rail. This was implemented using the NCP1014 from ON Semiconductor. The NCP1014 is a switching regulator with an integrated high-voltage switch. This IC enabled the reference design to achieve a standby power consumption that easily met the Energy Star and California Energy Commission (CEC) requirements cost effectively.

This reference design was targeted for the US model of the XBOX® Game Console. As a result, in order to keep the cost on parity to commercially available models, this reference design does not include a PFC section and is designed for the 110 Vac input. In order to meet the requirements in other regions, this design can be modified to include a PFC section as well.

Finally, though this reference design was targeted for the XBOX® Game Console, it can be easily adapted to fit the needs of other end applications. Since the main converter topology used for the reference design was the Active Clamp forward topology, the design can be modified to deliver much higher power requirements. A good example of a higher power design is available from ON Semiconductor's web site - a 305 W Desktop Power Supply (ATX) reference design using this same active clamp forward topology (Document Reference: TND313/D). Other applications such as game consoles with different output power requirements and other high power adapters are good candidates for adapting this reference design to meet specific requirements.



# TND331

## Introduction

Due to the ever increasing feature sets that are being integrated into game consoles and other consumer electronic devices, the power requirements for these devices is also increasing along with them. At the same time, numerous regulatory and market forces are driving the need for higher efficiencies from the power supplies of these devices. The active mode and standby mode efficiency targets of the

Energy Star and CEC programs for external power supplies are shown in Table 1 to Table 4. It should be noted that the Energy Star specifications are designed with the US market in mind. However, through its extensive partnership programs, several other countries and regions are implementing the Energy Star guidelines with very little changes.

**Table 1. Energy Star Energy Efficiency targets for Active Mode**

Nameplate Output Power ( $P_{no}$ )	Minimum Average Efficiency in Active Mode (expressed as decimal)
0 to < 1 Watt	$\geq 0.49 * P_{no}$
>1 and $\leq 49$ Watts	$\geq [0.09 * \ln(P_{no})] + 0.49$
> 49 Watts	$\geq 0.84$

**Table 2. Energy Star No-load Energy Consumption Criteria**

Nameplate Output Power ( $P_{no}$ )	Minimum Average Efficiency in Active Mode (expressed as decimal)
0 to <10 Watts	$\leq 0.5$ Watt
$\geq 10$ to $\leq 250$ Watts	$\leq 0.75$ Watt

**Table 3. CEC Requirements – Effective January 1, 2007**

Nameplate Output	Minimum Efficiency in Active Mode
0 to < 1 Watt	$0.49 * \text{Nameplate Output}$
>1 and $\leq 49$ Watts	$[0.09 * \ln(\text{Note 1}) (\text{Nameplate Output})] + 0.49$
> 49 Watts	0.84
<b>Maximum Energy Consumption in No-Load Mode</b>	
0 to <10 Watts	0.5 Watt
$\geq 10$ to $\leq 250$ Watts	0.75 Watt
Where $\ln(\text{Nameplate Output}) = \text{Natural Logarithm of the nameplate output expressed in Watts}$	

**Table 4. CEC Requirements – Effective July 1, 2008**

Nameplate Output	Minimum Efficiency in Active Mode
0 to < 1 Watt	$0.5 * \text{Nameplate Output}$
>1 and $\leq 51$ Watts	$[0.09 * \ln(\text{Note 1}) (\text{Nameplate Output})] + 0.5$
> 51 Watts	0.85
<b>Maximum Energy Consumption in No-Load Mode</b>	
Any output	0.5 Watt
Where $\ln(\text{Nameplate Output}) = \text{Natural Logarithm of the nameplate output expressed in Watts}$	

This reference design provides a solution to address the above challenges while meeting the aggressive specifications listed in the following section in a cost-effective manner.

1. "Ln" refers to the natural logarithm. The algebraic order of operations requires that the natural logarithm calculation be performed first and then multiplied by 0.09, with the resulting output added to 0.49. An efficiency of 0.84 in decimal form corresponds to the more familiar value of 84% when expressed as a percentage.

## Specifications

The target specifications for the reference design for several key parameters are outlined in this section.

### Input

- The Input Voltage range is 90 – 132 Vac, 47–63 Hz.
- Maximum steady state input current to be less than 5 A rms at 90 VAC for full load output.

### Output

- The output voltages for the power supply are 12 V and +5 V standby.
- The accuracy of the output voltage must be  $\pm 5\%$  or better at the load end of the connectors under all line and load conditions.
- The output ripple voltage of the power supply must not exceed 100 mVpp for 12 V output and 50 mVpp for +5 V STBY output.
- The reference design should be capable of supplying 203 W total output power under all specified conditions.
- The 12 V output should be capable of delivering 16.5 A of current (peak) with a maximum rating of 16.5 A. The 5 V STBY output should be capable of delivering a maximum of 1 A of current with a 1.5 A of peak.
- The output voltage hold-up time is 20 ms.

### Efficiency

- Active Mode Efficiency: The power supply efficiency will exceed 88% at 90 Vac and full load (measured at the end of PCB) for any ambient temperature within the operating range. The efficiency at 20% load and 90/115/132 Vac shall exceed 80% (at the end of the PCB).
- Standby Mode Efficiency: During main power off condition, the power supply unit will draw no more than 1 W from the AC outlet at 115 VAC, 60 Hz when a load of 0.5 W is applied to its +5V STBY rail.

### Protections

- Over Current
- Short Circuit
- Over Voltage
- Over Temperature

### Schematics

The schematics of the reference design are shown in this section. Figure 2 shows the schematic for the NCP1562 active clamp converter section of the reference design, Figure 3 shows the standby section and Figure 4 shows the control section.

# TND331




Figure 2. Main Board

TND331




Figure 3. NCP1014 - Standby Converter Section






Figure 4. NCP1562 – Active Clamp Forward Converter Section

# TND331

## Bill of Materials

The complete bill of materials for the power supply is given in this section.

**Table 5. Bill of Materials – Main Board**

REV:4			PRODUCT PART NO-SP001			
SL. NO	DESCRIPTION	CIRCUIT REF	PART VALUE	QTY/ UNIT	MANUFACTURER PART NO	MAKE
A	ASSEMBLY PCB, SS		ST200WA-V3		ST200WA-V3	MAX CIRCUITS
1	BRIDGE RECTIFIER	BR1	GBV806	1	VISHAY	
2	THERMISTOR, NTC	R13	2E, 15 mm	1	THINKING ELECTRONICS	
3	CAPACITOR, BOX, X2CLASS	C11	0.22 $\mu$ F, 275 V	1	VISHAY	
4	CAPACITOR, ELECTROLYTIC, +80%, -20%	C2	820 $\mu$ F, 250 V	1	JACKON / VISHAY	
5	CAPACITOR, ELECTROLYTIC, +80%, -20%	C3	4700 $\mu$ F, 25 V	1	JACKON / VISHAY	
6	CAPACITOR, ELECTROLYTIC, +80%, -20%	C4	100 $\mu$ F, 25 V	1	JACKON / VISHAY	
7	CAPACITOR, CERAMIC, Y2 CLASS	C5, C6, C7	2.2 nF, 250 V	3	EPCOS / VISHAY	
8	CAPACITOR, CERAMIC, MLC	C13	0.47 $\mu$ F, 100 V	1	VISHAY	
9	CAPACITOR, CERAMIC, MLC	C10, C14	0.1 $\mu$ F, 50 V	2	VISHAY	
10	CAPACITOR, CERAMIC, +20%, -20%	C8	103, 1 KV	1	VISHAY	
11	CAPACITOR, CERAMIC, +20%, -20%	C9	101, 1 KV	1	VISHAY	
12	CAPACITOR, CERAMIC, SMD2220	C27	1 $\mu$ F, 100 V	1	VISHAY / AVX	
13	CAPACITOR, CERAMIC, 1206	C32	10 nF, 50 V	1	VISHAY	
14	CAPACITOR, CERAMIC, 1206	C30	100 nF, 50 V	1	VISHAY	
15	RES, 5%, SMD, 1206	R1, R4	2E2	2	VISHAY	
16	RES, 5%, SMD, 1206	R6	10E	1	VISHAY	
17	RES, 5%, SMD, 1206	R3	2K2	1	VISHAY	
18	RES, 5%, SMD, 1206	R7, R14, R15	10K	3	VISHAY	
19	RES, 5%, SMD, 1206	R10	47E	1	VISHAY	
20	NICHROME WIRE	R5, R8	NICHROME WIRE	2	CUSTOM	10 mm
21	RES, 5%, CFR, 0.5W	R9	10E, 0.5 W	1	VISHAY	
22	RES, 5%, SMD, 2512	R12	0.05E	1	VISHAY	
23	RES, 5%, SMD, 2512	R11	0.018E	1	VISHAY	
24	DIODE, UFR, SOT23	D1, D2, D4	BAS16	3	ON Semiconductor	
25	DIODE, SMD MELF	R2	1N4148	1	NXP	CATHODE TOWARDS GATE OF Q1
26	DIODE, RECTIFIER	D10	1N4148	1	NXP	
27	RESISTOR, SMD, 1206	C31	0E	1		
28	ZENER DIODE, 400mW	D11, D12, D13, D14	16 V	4	ONSEMI / NXP	
29	TRANSISTOR, TO92	Q2	2SA1015	1	NXP	

# TND331

**Table 5. Bill of Materials – Main Board**

REV:4			PRODUCT PART NO-SP001			
SL. NO	DESCRIPTION	CIRCUIT REF	PART VALUE	QTY/ UNIT	MANUFACTURER PART NO	MAKE
<b>B</b>	<b>HEAT SINK</b>	<b>HS1</b>	<b>SP001HS1</b>	<b>1</b>	<b>CUSTOM</b>	<b>REF DRAWING</b>
1	MOSFET, TO220	Q1	STP4NK80ZP	1	ST	ALTERNATIVE

OR

1	MOSFET, TO220	Q1	STP3NK60ZP	1	ST	ALTERNATIVE
2	MOSFET, TO220	Q4	STP14NK50Z	1	ST	
3	TRIAC, TO220	Q6	BT139	1	NXP	
<b>C</b>	<b>HEAT SINK</b>	<b>HS2</b>	<b>SP001HS2</b>	<b>1</b>	<b>CUSTOM</b>	<b>REF DRAWING</b>
1	MOSFET, TO220	Q3, Q5	IRF3705N	2	IR	
D	COMMON MODE CHOKE	L8	12 $\mu$ H, 5 A	1	CUSTOM	
E	TOROID INDUCTOR	L3	40 $\mu$ H, 25 A	1	CUSTOM	
F	ASSEMBLY TRANSFORMER	T2	SP001ARD2	1	CUSTOM	
G	ASSEMBLY TRANSFORMER	T3	SP001DRVDR2	1	CUSTOM	
I	ASSEMBLY CHOKE	L10	3.3 $\mu$ H, 1.5 A	1	CUSTOM	
J	3PIN POWER CONNECTOR, PCB MOUNTABLE	J1	EMI30	1	ELCOM	

# TND331

**Table 6. Bill of Materials – Standby Converter Board**

REV:4			PRODUCT PART NO-SP001		
SL. NO	DESCRIPTION	CIRCUIT REF	PART VALUE	QTY/ UNITS	MAKE
<b>A</b>	<b>ASSEMBLY PCB, SS</b>		<b>AUXILLARY BOARD</b>		<b>CUSTOM</b>
1	CAPACITOR, CERAMIC, +20%, -20%	C12	102, 1 KV	1	EPCOS / VISHAY
2	CAPACITOR, CERAMIC, Y2 CLASS	C13	2.2 nF, 250 V	1	EPCOS / VISHAY
3	CAPACITOR, ELECTROLYTIC, +80%, -20%	C14, C24	100 µF, 25 V	2	JACKON / VISHAY
4	CAPACITOR, ELECTROLYTIC, +80%, -20%	C16, C17, C18	470 µF, 25 V	3	JACKON / VISHAY
5	CAPACITOR, ELECTROLYTIC, +80%, -20%	C22	10 µF, 50 V	1	JACKON / VISHAY
6	CAPACITOR, CERAMIC, X7R, SMD, 1206	C15, C20, C19, C21, C25	100 nF, 50 V	5	VISHAY
7	CAPACITOR, CERAMIC, X7R, SMD, 1206	C23	1 nF	1	VISHAY
8	RES, 5%, SMD, 1206	R13	22E	1	VISHAY
9	RES, 5%, SMD, 1206	R16	120E	1	VISHAY
10	RES, 1%, SMD, 1206	R17	2K2	1	VISHAY
11	RES, 1%, SMD, 1206	R20	6K8	1	VISHAY
12	RES, 1%, SMD, 1206 (T.S.R.)	R22	100K	1	VISHAY
13	RES, 1%, SMD, 1206	R23, R19	4K7	2	VISHAY
14	RES, 5%, CFR, 1W	R15	220K	1	VISHAY
15	DIODE, UFR	D5	1N5822	1	ON Semiconductor
16	DIODE, UFR	D6, D8	UF4005	2	VISHAY
17	DIODE, SCHOTTKY	D7	1N5819	1	ON Semiconductor
18	DIODE, RECTIFIER	D9	1N4007	1	ON Semiconductor
19	IC, DIP8, PWM SWITCHER	U1	NCP1014P	1	ON Semiconductor
20	IC, REF, TO92	U2	TL431	1	ON Semiconductor
21	IC, OPTOCOUPLER, DIP4	U8	PC817	1	FAIRCHILD SEMI
22	JUMPER	J1, J2, R14		3	
<b>B</b>	<b>ASSEMBLY TRANSFORMER</b>	<b>T1</b>	<b>STAUXSP001RD2</b>	<b>1</b>	<b>CUSTOM</b>
<b>C</b>	<b>ASSEMBLY CHOKE</b>	<b>L11</b>	<b>3.3 µH, 1.5 A</b>	<b>1</b>	<b>CUSTOM</b>
<b>D</b>	<b>BERG STICK 90° angle</b>	<b>J6, J7</b>	<b>7PIN</b>	<b>2</b>	<b>-</b>

# TND331

**Table 7. Bill of Materials – Active Clamp Forward Converter Board**

REV:4			PRODUCT PART NO-SP001		
SL. NO	DESCRIPTION	CIRCUIT REF	PART VALUE	QTY /	MAKE
			CONTROL BOARD	UNITS	
A	ASSEMBLY PCB, DS				CUSTOM
1	CAPACITOR, CERAMIC, X7R, SMD, 1206	C33, C34, C35, C37, C40, C44, C46 (Note 2)	100 nF, 50 V	7	VISHAY
2	CAPACITOR, CERAMIC, X7R, SMD, 1206	C28	10 nF, 50 V	1	VISHAY
3	CAPACITOR, CERAMIC, X7R, SMD, 1206	C39	10 nF, 50 V	1	VISHAY
4	CAPACITOR, CERAMIC, X7R, SMD, 1206	C29	470 pF, 50 V	1	VISHAY
5	CAPACITOR, CERAMIC, MLC	C26	0.47 μF, 50 V	1	VISHAY
6	CAPACITOR, CERAMIC, X7R, SMD, 1206	C31	220 pF, 50 V	1	VISHAY
7	CAPACITOR, CERAMIC, X7R, SMD, 1206	C32	330 pF, 50 V	1	VISHAY
8	CAPACITOR, CERAMIC, X7R, SMD, 1206	C38	1 nF, 50 V	1	VISHAY
9	CAPACITOR, ELECTROLYTIC, +80%, -20%	C45	10 μF, 63 V	1	JACKON/VISHAY
10	CAPACITOR, ELECTROLYTIC, +80%, -20%	C43	4.7 μF, 63 V	1	JACKON/VISHAY
11	RES, 5%, SMD, 1206	R24, R26, R28	2M	3	VISHAY
12	RES, 5%, SMD, 1206	R30	160K	1	VISHAY
13	RES, 1%, SMD, 1206	R25, R27, R29, R40	100K	4	VISHAY
14	RES, 1%, SMD, 1206	R31	27K	1	VISHAY
15	RES, 1%, SMD, 1206	R32, R59	470K	2	VISHAY
16	RES, 5%, SMD, 1206	R33, R39, R53, R55	1K	4	VISHAY
17	RES, 5%, SMD, 1206	R34, R56	3.3K	2	VISHAY
18	RES, 1%, SMD, 1206	R35	820E	1	VISHAY
19	RES, 1%, SMD, 1206	R36	220E	1	VISHAY
20	RES, 1%, SMD, 1206	R37, R60	39K	2	VISHAY
21	RES, 1%, SMD, 1206 (T.S.R.)	R64	120K	1	VISHAY
22	RES, 5%, SMD, 1206	R38, R54, R61, R62	2.2K	4	VISHAY
23	RES, 5%, SMD, 1206	R50	1.5K	1	VISHAY
24	RES, 1%, SMD, 1206	R52, R58, R63, R65	10K	4	VISHAY
25	TRIMPOT, MULTITURN	R44	10K	1	BOURNS
26	RES, 1%, SMD, 1206	R43, R57	18K	1	VISHAY
27	RES, 1%, SMD, 1206	R51	220K	1	VISHAY
28	RES, 1%, SMD, 1206 (Note 3)	R66	20K	1	VISHAY
29	DIODE, UFR, SOT23	D12, D13	BAS16	2	ON Semiconductor
30	TRANSISTOR, TO92	Q7	2N2222A	1	ON Semiconductor
31	SCR, TO92	Q8	2N6565	1	NXP
32	IC, SO-16, PWM SWITCHER	U3	NCP1562A	1	ON Semiconductor
33	IC, REF, TO92	U5, U6	TL431	2	ON Semiconductor
34	IC, OP-AMP SOP14	U7	LM324	1	ON Semiconductor
35	IC, OPTOCOUPLER, DIP4	U9, U10	PC817	2	FAIRCHILD SEMI
36	NOT USED	R42, R45, R46, R47, R48, R49, C42, D11, C36		8	
B	BERG STICK 90° angle	J1, J2	7PIN	2	
C	HEAT SINK (Note 4)	HS3	SP001HS3U	1	CUSTOM

2. MOUNT C46 ON R58

3. PCB FOOT PRINT NOT AVAILABLE, SOLDER DIRECTLY ACROSS THE CHIP

4. OUTER HEATSINK

# TND331

## Performance Results

### Efficiency

Efficiency at Different Line and Load Conditions			
Input Voltage	20% Load	50% Load	100% Load
90 Vac	88.45%	90.54%	88.48%
100 Vac	87.84%	90.40%	88.89%
110 Vac	87.26%	90.26%	89.09%
120 Vac	85.71%	90.15%	89.71%
130 Vac	85.49%	90.35%	90.04%

### Standby Power

The measured input (standby) power at 110 Vac and no load on the outputs (with 12 V output disabled) is 488 mW.

### Ripple Measurements

The measured p-p ripple for the 12 V output was 80 mV p-p (max) and the ripple for the 5 V output is 30 mV p-p (max).

Start-up and Shutdown Waveforms

Output turn on and off waveforms.




Figure 5. Output Turn On Waveform




Figure 6. Output Turn On Waveform




Figure 7. Output Turn On Waveform




Figure 8. Output Turn Off Waveform




Figure 9. Output Turn Off Waveform




Figure 10. Transient Response

# TND331




Figure 11. Board Picture

## Magnetic Component Information

### 1. Driver Transformer: SP001DRVDR2

1. Transformer Core: EE16

2. Bobbin: EE16 VERTICAL 3+3 Pins

SI No.	Winding Description	Turns	No Of Wires	SWG	Layers	Start	Finish
1	Primary winding W1	18	2	30	1	3	1
2 Layers of 2 Mil Tape Insulation							
2	Secondary winding W2	40	2	30	1	6	4

### 2. Auxiliary / Standby Power Supply Transformer: STAUXSP001RD2

1. Transformer Core: EFD20

2. Bobbin: EFD20 Horizontal 4+4 Pins

SI No.	Winding Description	Turns	No Of Wires	SWG	Layers	Start	Finish
1	Primary winding W1	102	1	32	1	3	1
2 Layers of 2 Mil Tape Insulation							
2	Bias Winding W2	12	1	28	1	4	2
2 Layers of 2 Mil tape Insulation							
3	Secondary Winding W3	5	3	28	1	8	7
2 Layers of 2 Mil tape Insulation							
4	Secondary Winding W4	12	1	28	1	6	5

Gap Length: 3.15 mils.

Primary Inductance: 2055  $\mu$ H

Estimated Transformer Primary Leakage Inductance to be less than 5% of Primary Inductance



# TND331

## 3. Main Transformer: SP001ARD2


1. Transformer Core: PQ 32/20

2. Bobbin: PQ 32/20, 6 + 6 Pins

SN	Winding Description	Turns	No.of wires	SWG	Layers	Start	Finish
1	Split Primary Winding W1	7	8	0.4/0.5 mm	1	2,3	FL1
2 Layers of 2 Mil Tape Insulation							
2	Gate drive winding W2	2	2	28	1	7	9
3	Gate drive winding W3	1	2	28	1	9	12
2 Layers of 2 Mil Tape Insulation							
4	Secondary Winding W4	3	-	10 Mils foil, 16 mmWidth	1	10, 11	8
Note: For winding 4 use 15SWG Wire leads to solder the foil							
2 Layers of 2 Mil Tape Insulation							
5	Split Primary winding W5	6	8	0.4/0.5 mm	1	FL1	4, 5

Primary Inductance 900 $\mu$ H across pins 2 & 5, + 0%, - 10%
Estimated Transformer Primary Leakage Inductance to be less than 5% of Primary.
Wind Uniformly all windings @ spread it evenly across the entire cross section of the bobbin

## 4. Output Inductor: T27



Toroid	T27- MicroMetal
Wire gauge	15 SWG, 2 wires, 15 Turns
Inductance	40 $\mu$ H
Amps	20 A

### Potential Improvements

In evaluating the results of the reference design, certain areas of further performance improvements are identified and listed below.

- The drive circuit for the active clamp and the main FET can be simplified using the integrated high-side / low-side driver like the NCP5181 instead of the gate drive transformer.


- The thermal performance and efficiency can be further improved by choosing more optimal FETs for the secondary synchronous rectifiers and also by optimizing the drive circuit for these devices. It is estimated that there is additional power loss of 1-2% in the current design that is attributable to the inefficient switching of the synchronous rectifiers.

## APPENDIX

## References:

- Draft Commission Communication on Policy Instruments to Reduce Stand-by Losses of Consumer Electronic Equipment (19 February 1999)
    - [http://energyefficiency.jrc.cec.eu.int/pdf/consumer\\_electronics\\_communication.pdf](http://energyefficiency.jrc.cec.eu.int/pdf/consumer_electronics_communication.pdf)
  - European Information & Communications Technology Industry Association
    - <http://www.eicta.org/>
  - <http://standby.lbl.gov/ACEEE/StandbyPaper.pdf>
- CECP (China):
- <http://www.cecp.org.cn/englishhtml/index.asp>
- Energy Saving (Korea):
- <http://weng.kemco.or.kr/efficiency/english/main.html#>
- Top Runner (Japan):
- [http://www.eccj.or.jp/top\\_runner/index.html](http://www.eccj.or.jp/top_runner/index.html)
- EU Eco-label (Europe):
- [http://europa.eu.int/comm/environment/ecolabel/index\\_en.htm](http://europa.eu.int/comm/environment/ecolabel/index_en.htm)
  - [http://europa.eu.int/comm/environment/ecolabel/product/pg\\_television\\_en.htm](http://europa.eu.int/comm/environment/ecolabel/product/pg_television_en.htm)
- EU Code of Conduct (Europe):
- [http://energyefficiency.jrc.cec.eu.int/html/standby\\_initiative.htm](http://energyefficiency.jrc.cec.eu.int/html/standby_initiative.htm)
- GEEA (Europe):
- <http://www.efficient-appliances.org/>
  - <http://www.efficient-appliances.org/Criteria.htm>
- Energy Star:
- <http://www.energystar.gov/>
  - [http://www.energystar.gov/index.cfm?c=product\\_specs.pt\\_product\\_specs](http://www.energystar.gov/index.cfm?c=product_specs.pt_product_specs)
- 1 Watt Executive Order:
- <http://oahu.lbl.gov/>
  - [http://oahu.lbl.gov/level\\_summary.html](http://oahu.lbl.gov/level_summary.html)

GreenPoint is a trademark of Semiconductor Components Industries, LLC (SCILLC).

**ON Semiconductor** and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## PUBLICATION ORDERING INFORMATION

## LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor  
 P.O. Box 5163, Denver, Colorado 80217 USA  
**Phone:** 303-675-2175 or 800-344-3860 Toll Free USA/Canada  
**Fax:** 303-675-2176 or 800-344-3867 Toll Free USA/Canada  
**Email:** [orderlit@onsemi.com](mailto:orderlit@onsemi.com)

**N. American Technical Support:** 800-282-9855 Toll Free  
 USA/Canada  
**Europe, Middle East and Africa Technical Support:**  
 Phone: 421 33 790 2910  
**Japan Customer Focus Center**  
 Phone: 81-3-5773-3850

**ON Semiconductor Website:** [www.onsemi.com](http://www.onsemi.com)

**Order Literature:** <http://www.onsemi.com/orderlit>

For additional information, please contact your local Sales Representative